

[See all 20 Products in Family](#)

Effilux White EFFI-Lase Structured LED Lighting Projector with Line Pattern



Effilux EFFI-Lase Structured LED Lighting Projector

Stock **#22-118** 1 In Stock

-

1

+

A\$1,793⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	A\$1,793.00 each
Need More?	Request Quote

Note: This item requires accessories for use | [Learn More](#)

Product Downloads

General	
EFFI-LASE-PSV-LX1-000-ZZZ	Model Number:
LED Illuminator	Type of Illumination:
Effilux	Manufacturer:
3D Projector	Geometry:

Illumination Mode:	
Strobe or Constant	
Physical & Mechanical Properties	
Dimensions (mm):	
79.1 x 129.6	
Optical Properties	
Color:	
White	
Hardware & Interface Connectivity	
Power Supply:	
Power Supply Required and Sold Separately:	
USA: #15-874	
Europe: #15-875	
Japan: #73-409	
Korea: #73-409	
China: #15-874	
Environmental & Durability Factors	
Operating Temperature (°C):	
0 to 40	
Regulatory Compliance	
RoHS 2015:	
Compliant	
Reach 224:	
Compliant	
Certificate of Conformance:	
View	

Product Details

- High Accuracy Without Speckle
 - Wide Range of Standard Masks Available
 - White, Blue, Red, and IR Colors Available
 - Compatible with [C Series Fixed Focal Length Lenses](#) and [HP Series Fixed Focal Length Lenses](#) for Pattern Projection
- Effilux EFFI-Lase Structured LED Lighting Projectors produce accurate, intense, and uniform lines, matrices, crosses, and arrays of points. Featuring an integrated driver board and easily interchangeable masks, these projectors are ready for plug and play use. Passive cooling and a temperature protection system ensure stable operation and help to prevent damage for long term operation. Effilux EFFI-Lase Structured LED Lighting Projectors offer the accuracy, power, and homogeneity of a laser projector without the speckle. These projectors are ideal for a range of machine vision applications such as 3D reconstruction, stereovision, and alignment.
- Note:** Masks sold separately, see accessories tab for options. Designed for use with a C-mount lens for pattern projection. 1.1" sensor lenses are recommended for masks with rectangular patterns to reduce distortion while 2/3" sensor lenses are sufficient for all other applications.