


TECHSPEC®

Elliptical Mirror 47.63mm Minor Axis Enhanced Aluminum



Stock #32-135

CONTACT US

-

1

+

A\$297.60

ADD TO CART

Qty 1-5

A\$297.60

Qty 6+

A\$238.40

Volume Pricing

[Request Quote](#)

Get Product Downloads



Minor Axis (mm):

47.63

Major Axis (mm):

67.36

Surface Flatness (P-V):

$\lambda/8$

Substrate:

BOROFLOAT®
Surface Quality: 60-40
Dimensional Tolerance (mm): ±0.38
Dimensional Tolerance (inches): ±0.015
Coating Specification: R _{avg} >95% @ 450 - 650nm
Coating: Enhanced Aluminum (450-650nm)
Coating Type: Metal
Clear Aperture CA (mm): 42.88 (Minor Axis) 60.63 (Major Axis)
Note: Flatness specification is Peak to Valley
Thickness (mm): 11.68
Thickness Tolerance (inches): ±0.040
Thickness Tolerance (mm): ±1.02
Type: Flat Mirror
Wavelength Range (µm): 0.45 - 0.65
Wavelength Range (nm): 450 - 650
Damage Threshold, Reference: ☐ 0.2 J/cm² @ 532nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant