

IDS GV-77U5WP-C-HQ, 10GigE, 2" Color Camera

See More by [IDS Imaging Development Systems](#)



IDS Imaging uEye Warp10 10GigE Cameras

Stock **#73-556** [CONTACT US](#)

-

1

+

A\$14,336^{.00}

ADD TO CART

Volume Pricing	
Qty 1+	A\$14,336.00 each
Need More?	Request Quote

Product Downloads

Color	Spectrum:
General	
Color Camera	Type:
GV-77U5WP-C-HQ	Model Number:
IDS Imaging Development Systems	Manufacturer:
	Camera Series:

Physical & Mechanical Properties

Dimensions (mm): 60 x 75 x 94.5 (excludes connectors and lens mount)	
Weight (g): 570	
Housing: Full	

Sensor

Image Buffer: 2032	
Sensor Format: 2"	
Resolution (Megapixels): 44.84	
Frame Rate (fps): 17.00	
Pixels (H x V): 8,192 x 5,460	
Pixel Size, H x V (µm): 3.20 x 3.20	
Sensing Area, H x V (mm): 26.214 x 17.472	
Imaging Sensor: On Semi XGS 45000	
Type of Sensor: Progressive Scan CMOS	
Shutter Type: Global	
Pixel Depth: 12 bit	
Exposure Time: 0.037ms - 2000ms	
Dynamic Range (dB): 66.00	
Machine Vision Standard: GigE Vision	

Electrical

Power Consumption (W): 12.7 - 16.7	
---------------------------------------	--

Hardware & Interface Connectivity

Interface: 10GigE (PoE)	
Connector: GigE RJ45	
Power Supply: Power over Ethernet (PoE) or via GPIO	
GPIOs: 1 Trigger Input, 1 Flash Output, 2 Fast Output	
Interface Port Orientation: Back Panel	
GPIO Connector Type: 12-pin M12 connector (Attend 216A-12MSR)	

Threading & Mounting

Mount: TFL-Mount	
Mounting Threads: ¼-20 with Tripod Mount Adapter #16-017	

Environmental & Durability Factors

Operating Temperature (°C): 0 to +55	
Storage Temperature (°C): -20 to +60	

Regulatory Compliance

RoHS 2015: Exempt	
Certificate of Conformance: View	

Product Details

- 10GBASE-T (10GigE) Ethernet Interface, 10X Faster than GigE
- Up to 12.3MP Resolution with Framerrates up to 98fps
- Compatible with 1GigE, 2.5GigE and 5GigE Interfaces

IDS Imaging uEye Warp10 10GigE Cameras are capable of providing high quality, reliable image transfers at cable lengths of up to 100m on CAT6A or 40m on CAT5e. These global shutter cameras offer up to 12.3MP resolution. The 10GigE Ethernet interface provides up to 10X faster speeds than GigE for framerates up to 98fps for applications requiring high bandwidth. IDS Imaging uEye Warp10 10GigE Cameras are backwards compatible with existing 1GigE, 2.5GigE or 5GigE interfaces and will adjust their speed automatically. These cameras are ideal for machine vision, metrology, electronics inspection, and sports/motion analysis applications. These GeniCam compliant cameras are designed for the [IDS Peak software](#) but are compatible with most other GeniCam software protocols.