

[See all 65 Products in Family](#)

IDS U3-3040LE-M-GL, USB 3.0, 1/2.9" Monochrome Camera

See More by [IDS Imaging Development Systems](#)



IDS Imaging uEye LE/XLE Camera (C/CS - Mount, Full Housing, Front View)



Stock #24-104 **1 In Stock**

[Similar Cameras](#)

− 1 + A\$620⁰⁰

ADD TO CART

Volume Pricing

Qty 1+	A\$620.80 each
Need More?	Request Quote

Product Downloads

Monochrome

Spectrum:

General

Monochrome Camera

Type:

U3-3040LE-M-GL

Model Number:

Manufacturer:
IDS Imaging Development Systems

Camera Series:
uEye+ LE

Physical & Mechanical Properties

Dimensions (mm):
47 x 46 x 23.9 (excludes connectors and lens mount)

Weight (g):
38

Housing:
Full

Sensor

Image Buffer:
Not Specified

Sensor Format:
1/2.9"

Resolution (Megapixels):
1.58

Frame Rate (fps):
230.00

Pixels (H x V):
1,448 x 1,086

Pixel Size, H x V (µm):
3.45 x 3.45

Sensing Area, H x V (mm):
4.995 x 3.746

Imaging Sensor:
Sony IMX273

Type of Sensor:
Progressive Scan CMOS

Shutter Type:
Global

Pixel Depth:
12 bit

Exposure Time:
0.04ms - 2000ms

Dynamic Range (dB):
70.00

Machine Vision Standard:
USB3 Vision

Electrical

Power Consumption (W):
1 - 2

Hardware & Interface Connectivity

Interface:
USB 3.0

Connector:
USB Type-C

Power Supply:
Power over USB

GPIOs:
N/A

Synchronization:
Hardware Trigger (GPIO); Software Trigger

Interface Port Orientation:
Back Panel (Right Angle)

GPIO Connector Type:
No GPIO Connector Available

Threading & Mounting

Mount:
C/CS-Mount

Mounting Threads:
¼-20 with Tripod Mount Adapter [#16-017](#)

Environmental & Durability Factors

Operating Temperature (°C):
0 to +55

Storage Temperature (°C):
-20 to +80

Regulatory Compliance

[Exempt](#) **RoHS 2015:**

[View](#) **Certificate of Conformance:**

[Contains SVHC\(s\)](#) **REACH 241:**

Product Details

- Up to 8.0MP Resolution with Framrates up to 230fps
- Board Level Options with C/CS-Mount or S-Mount Available
- GenICam USB3 Vision Compliant

IDS Imaging uEye LE/XLE USB3.1 Cameras utilize [IDS Imaging's peak SDK platform](#) that supports GenICam and USB3 Vision standards for ease of software development and integration. These cameras are available in board-level or housed options with S-Mount or C/CS-Mount versions. The C/CS-Mount configurations come with a 5mm spacer to easily adapt between C-Mount and CS-Mount lenses. IDS Imaging uEye LE/XLE USB3.1 Cameras are ideal for small device construction, medical technology, robotics, and machine vision applications. With a compact design, the XLE version is suitable for integration into embedded systems whereas the LE version is suitable for small device projects.

;