

FC-APC Singlemode Patchcord, 2m Length



Stock **#55-491** CLEARANCE CONTACT US

-

1

+

A\$102⁻⁴⁰

ADD TO CART

Volume Pricing	
Qty 1+	A\$102.40 each
Need More?	Request Quote

Product Downloads

SPECIFICATIONS

General

Patchcord

Type:

Physical & Mechanical Properties

125.00

Cladding Diameter (μm):

8.2

Core Diameter (μm):


Construction:	
Yellow PVC Jacket Singlemode	
Optical Properties	
Substrate: 	
Hardware & Interface Connectivity	
Connector:	
FC/APC	
Loss (dB):	
<0.3 insertion, <-65 return	
Environmental & Durability Factors	
Operating Temperature (°C):	
-40 to +75	
Storage Temperature (°C):	
-55 to +85	
Regulatory Compliance	
Certificate of Conformance:	
View	




PRODUCT DETAILS


- UV/MS and VIS/NIR Versions Available
- FC Connector Compatible with [Spatial Filters](#)
- FC Connector Compatible with [Fiber Alignment Mounts](#)
- FC and SMA Connector Options

High Quality Fiber Patchcords are designed for UV-VIS (190 - 1250nm) or VIS-NIR (300 - 2400nm) ranges. These Patchcords are 1.5 meters in length with Nylon or Tefzel coatings. With core diameters ranging from 50 – 1000µm, these patchcords provide quality solutions for a variety of core sizes. High Quality Fiber Patchcords are available with SMA905 or FC/PC connectors featuring a 0.22 numerical aperture. These Patchcords are ideal for applications requiring optimum transmission in the UV-VIS or VIS-IR wavelengths.

TECHNICAL INFORMATION







Non-Flange Type

units: mm

