

TECHSPEC® Finite Conjugate, UV Coated, 10X/0.23NA RefIX Objective



Stock #89-725 [CONTACT US](#)

-

1

+

A\$3,214.40

ADD TO CART

Qty 1+
A\$3,214.40
Qty 2+
A\$2,832.00
Volume Pricing
Request Quote

Get Product Downloads

Entrance Pupil Position (mm):
8.4641 (Diameter)

Horizontal Field of View, 1/2" Sensor:
0.64mm

Horizontal Field of View, 2/3" Sensor:
0.88mm

Focal Length FL (mm):
18.40

Coating: Enhanced Aluminum (200-11000nm)
Magnification: 10X
Numerical Aperture NA: 0.23
Mounting Threads: RMS
Type: Microscope Objective
Obscuration (%): 27.00
Transmitted Wavefront, RMS: λ/10
Diameter of Small Mirror (mm): 8.9
Working Distance (mm): 30.56
Aperture Diameter (mm): 8.6
Coating Specification: R _{avg} >85% @200 - 700nm (typical) R _{avg} >76% @ 700 - 1750nm (typical) R _{avg} >96% @ 1750 - 11000nm (typical)
Wavelength Range (nm): 200 - 11000
Style: Finite Conjugate
Manufacturer: Edmund Optics®
Flange Distance (mm): 150

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View