

# InfiniGage Precision Spacer Kit

See More by [Infinity Photo-Optical Company](#)



Stock #62-851 [CONTACT US](#)

1 [-](#) [+](#) A\$665<sup>00</sup>

**ADD TO CART**

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1+         | A\$665.60 each                |
| Need More?     | <a href="#">Request Quote</a> |

## Product Downloads

## General

Lens Accessory **Type:**  
**Compatible Lens:**  
[#62-830 & #62-831](#)

## Regulatory Compliance

**RoHS 2015:**  
[Compliant](#)  
**Reach 224:**  
[Compliant](#)

## Product Details

- Accurate Measurements Based on Field of View
- 7 Spacer Options for a Wide Range of Magnifications
- UV Option Available

The InfiniGage™ main lens mates with seven precision spacers for multiple magnification and working distance choices. Simply set InfiniGage™ to the desired magnification and begin making accurate measurements. The InfiniGage™ accepts 11.8mm to 12.5mm diameter filters for polarization or color analysis without changing outer dimensions. The InfiniGage™ can be doubled in magnification by simply adding a DL Doubler Tube, reducing the FOV by a factor of two. The InfiniGage™ is also available in UV which is optimized for best performance from 250nm-700nm.

**Note:** InfiniGage™ CW option is only compatible with CW Precision Spacers.

## Technical Information

|  | Magnification | Working Distance | Field of View on 1/2" Sensor | Field of View on 1/3" Sensor |
|--|---------------|------------------|------------------------------|------------------------------|
| InfiniGage Precision Spacer with 2X Amplifier (Optional) | 0.25X         | 286mm            | 25.6mm                       | 19.2mm                       |
|  | 0.5X          | 155mm            | 12.8mm                       | 9.6mm                        |
|  | 0.66X         | 120mm            | 9.7mm                        | 7.3mm                        |
|  | 1.0X          | 85mm             | 6.4mm                        | 4.8mm                        |
|  | 1.3X          | 72mm             | 4.9mm                        | 3.6mm                        |
|  | 1.5X          | 67mm             | 4.3mm                        | 3.2mm                        |
|  | 2.0X          | 52mm             | 3.2mm                        | 2.4mm                        |