

TECHSPEC® Infinite Conjugate, DUV Coated, 15X/0.28NA HP ReflX



High Performance ReflX™ Objectives

Stock #59-884 3-5 DAYS

⊖ 1 ⊕ **A\$3,934.40**

ADD TO CART

Qty 1+
A\$3,934.40
Qty 2+
A\$3,472.00
Volume Pricing
Request Quote

Get Product Downloads

Entrance Pupil Position (mm):
51.8

Horizontal Field of View, 1/2" Sensor:
0.43mm

Horizontal Field of View, 2/3" Sensor:
0.59mm

Focal Length FL (mm):

13.30
Coating: DUV Enhanced Aluminum (150-11000nm)
Magnification: 15X
Mount: RMS
Numerical Aperture NA: 0.28
Type: Microscope Objective
Obscuration (%): 27.00
Transmitted Wavefront, RMS: λ/14
Diameter of Small Mirror (mm): 8.8
Working Distance (mm): 23.75
Aperture Diameter (mm): 8.5
Note: Requires a 200mm secondary tube lens Entrance Pupil Position specification is measured in mm from flange
Coating Specification: R _{avg} >83% @ 150 - 1000nm (typical) R _{avg} >94% @ 1000 - 11000nm (typical)
Wavelength Range (nm): 150 - 11000
Style: Infinity Corrected
Manufacturer: Edmund Optics®

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View