

fNIRS Standard Phantom - IEC 80601-2-71



fNIRS Standard Phantom - IEC 80601-2-71

Stock #91-290 NEW **1 In Stock**

A\$8,552⁰⁰

ADD TO CART

Volume Pricing

Qty 1+	A\$8,552.00 each
Need More?	Request Quote

Product Downloads

General

Type: fNIRS

Contents of Kit:
fNIRS standard phantom, 20 dB attenuator, c mount adapter, instruction, datasheet

Physical & Mechanical Properties

Weight (g): 571.8

Dimensions (mm):
Phantom block: 70 x 70 x 40 mm (length x width x

height)

Regulatory Compliance

[Compliant](#)

RoHS 2015:

[View](#)

Certificate of Conformance:

Product Details

- Realistic Optical and Anatomical Properties for Accurate Calibration and Validation of Optical Imaging Systems
- Available in Versions Suited For fNIRS, Fluorescence Imaging, And Diffuse Correlation Spectroscopy Applications
- fNIRS Version Enables Standardized, Repeatable Performance Testing and Regulatory Compliance (IEC 80601-2-71)
- Supports Life Science and Medical Device Research Focused on Brain-Related Optical Imaging

Anthropomorphic fNIRS Phantoms offer a comprehensive set of reference models for validating and benchmarking optical imaging systems in brain-related and life science research. This includes homogeneous adult and infant head phantoms that replicate the optical and anatomical properties of human tissue, and an infant hollow head phantom that allows for internal source placement or component testing. For more advanced performance evaluations, the Dynamic Liquid Phantom mimics micro-vasculature using a flow system with a liquid-filled channel, pump, and control hardware—allowing researchers to study how light interacts with moving or absorbing media and to assess imaging depth, absorption sensitivity, and spatial resolution. In addition, the fNIRS Phantom, designed in compliance with IEC 80601-2-71, provides a standardized reference for evaluating fNIRS system performance. These phantoms are ideal for researchers and medical device developers, delivering standardized, compliant tools that support reliable, reproducible imaging performance.

;