

[See all 14 Products in Family](#)

LightPath 390037 | 5.5mm Dia., 0.85 NA, BBAR (1800-3000nm), Molded IR Aspheric Lens

See More by [Lightpath®](#)



Stock #66-564 CLEARANCE **1 In Stock**

[Other Coating Options](#)

A\$337⁵²

ADD TO CART

| Volume Pricing | |
|----------------|-------------------------------|
| Qty 1+ | A\$337.52 each |
| Need More? | Request Quote |

Product Downloads

General

390037 **Lightpath Lens Code:**

Aspheric Lens **Type:**

Physical & Mechanical Properties

5.50 ±0.015 **Diameter (mm):**

4.00 **Clear Aperture CA (mm):**

| | |
|----------------------|----------------------------------|
| 2.24 | Edge Thickness ET (mm): |
| 3.00 | Center Thickness CT (mm): |
| Protective as needed | Bevel: |

Optical Properties

| | |
|---------------------------------------------------------------------------|----------------------------------------------------|
| 1.87 @ 9500nm | Effective Focal Length EFL (mm): |
| 0.85 | Numerical Aperture NA: |
| Black Diamond™ BD-2 (Ge ₂₈ Sb ₁₂ Se ₆₀) | Substrate: <input type="checkbox"/> |
| 9500 | Aspheric Design Wavelength (nm): |
| BBAR (1800-3000nm) | Coating: |
| R _{avg} < 1.0% @ 1.8 - 3.0μm | Coating Specification: |
| 80-50 | Surface Quality: |
| 0.58 | f#: |
| 2.6023 | Index of Refraction (n_d) @ 10μm: |
| 2.5843 | Index of Refraction (n_d) @ 14μm: |
| 2.6210 | Index of Refraction (n_d) @ 4μm: |
| 2.6173 | Index of Refraction (n_d) @ 5μm: |
| 1800 - 3000 | Wavelength Range (nm): |
| 0.72 | Working Distance (mm): |
| Infinite | Conjugate Distance: |
| 9500 | Focal Length Specification Wavelength (nm): |

Material Properties

| | |
|----------------------------------------------------------|-------------------------------------------------------------------|
| 14.00 | Coefficient of Thermal Expansion CTE (10⁻⁶/°C): |
| 4.68 | Density (g/cm³): |
| 70 x 10 ⁻⁶ /°C from -40° to +80°C (5 - 14 μm) | Thermo-optic coefficient dn/dT: |
| 285.00 | Transformation Temperature (°C): |

Regulatory Compliance

| | |
|---------------------------|------------------------------------|
| Compliant | RoHS 2015: |
| View | Certificate of Conformance: |
| Compliant | Reach 233: |


Product Details

- Wavelength Range of 1.8 - 12μm
- Variety of Coating Options
- Mounted and Unmounted Versions

LightPath® Mid-Wave and Long-Wave Infrared (IR) Aspheric Lenses feature a low-cost, molded design and offer several key benefits over Germanium substrate aspheres. With a dn/dT and CTE significantly less than that of Germanium, the lenses feature a smaller change in focal length as a function of temperature change. Featuring a higher operating temperature than Germanium (which suffers 20 – 30% transmission loss at 100°C), the lenses can be used in applications including collimators for QCL lasers and as components within thermal imaging assemblies. LightPath Mid-Wave and Long-Wave Infrared (IR) Aspheric Lenses have a wavelength range of 1.8 - 12μm. These lenses are available mounted or unmounted, in a variety of coating options.

Technical Information

1.8 - 3 μ m AR Coating



;