

Harsh Environment Transmission Dip Probe Tip, 25 mm

See More by [Ocean Optics](#)



Stock **#90-581** NEW **1 In Stock**

-

1

+

A\$883²⁰

ADD TO CART

Volume Pricing	
Qty 1+	A\$883.20 each
Need More?	Request Quote

Product Downloads

Construction Material:	
Titanium	

General

Model Number:	
RT-TI-25MM	

Optical Properties

Wavelength Range (nm):	
200 - 2500	

Regulatory Compliance

RoHS 2015:	
Compliant	

Certificate of Conformance:	
View	

Reach 250:	
Compliant	

Product Details

- Transmission Dip Probes Designed for Reliable In-Solution Absorbance/Transmission Measurements
- Rugged Stainless Steel or PEEK for Tough Process Conditions and Harsh Environments
- Flexible Path Lengths Available with Interchangeable Probe Tips
- Compatible with Ocean Optics Spectrometers and Accessories

Ocean Optics Transmission Dip Probes couple to spectrometers and light sources to measure absorbance and transmission in solutions. Choose from ruggedized high-pressure probe ([#90-569](#)) for demanding process environments or PEEK-jacketed probes ([#90-570](#) and [#90-571](#)) for harsh chemical conditions, spanning UV–VIS to VIS–NIR wavelengths. Easily customize your setup with accessories such as interchangeable probe tips in various path lengths and the protective sleeve ([#90-585](#)) for extended durability in corrosive or high-temperature applications. Ocean Optics Transmission Dip Probes are designed for seamless integration with [Ocean Optics spectroscopy systems and compatible accessories](#).