

[See all 15 Products in Family](#)

# Coherent® EnergyMax 1191435 | 500nJ-600µJ, USB

See More by [Coherent®](#)



Coherent® EnergyMax Laser Energy Sensors

Stock #88-422 [CONTACT US](#)

⊖ 1 ⊕ A\$4,328<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1+	A\$4,328.00 each
Need More?	<a href="#">Request Quote</a>

## Product Downloads

### General

**Model Number:**  
J-10MB-LE  
Coherent Part Number: 1191435

**Type:**  
Meterless

**Linearity (%):**  
±3

**Calibration Uncertainty (%):**  
±2

Noise Equivalent Energy ( $\mu\text{J}$ ):

<0.05

Maximum Incident Energy Density:

500mJ/cm<sup>2</sup> (10ns, 1064nm)

Energy Range:

500nJ - 600 $\mu\text{J}$

## Physical & Mechanical Properties

Active Area Diameter (mm):

10

## Optical Properties

Calibration Wavelength (nm):

1064

Maximum Pulse Width ( $\mu\text{s}$ ):

17

Wavelength Range (nm):

190 - 12000

## Sensor

Type of Sensor:

Pyroelectric

## Electrical

Maximum Repetition Rate (pps):

1000

Maximum Incident Beam Power (W):

4

## Hardware & Interface Connectivity

Connector:

USB

Length of Cable (m):

3.0

## Regulatory Compliance

RoHS 2015:

[Exempt](#)

Reach 224:

[Contains SVHC\(s\)](#)

Certificate of Conformance:

[View](#)

## Product Details

- ISO 17025 Certified
- Embedded Spectral Compensation Characteristics
- Automatic Temperature Compensation

Coherent® EnergyMax Laser Energy Sensors are designed for a variety of demanding laser measurement applications. These energy sensors, available in meter or meterless USB configurations, incorporate a diffuse coating to minimize specular reflection and feature large active areas. The J-50MB-YAG combines the MaxBlack coating with a diffuser for use with high energy lasers of up to 3J. Coherent® EnergyMax Laser Energy Sensors utilize onboard sensors to automate temperature compensation for improved measurement accuracy.