

Coherent® EnergyMax 1191437 | Nd:YAG Sensor, 2.4mJ-3J, USB

See More by [Coherent®](#)



Coherent® EnergyMax Laser Energy Sensors

Stock **#88-421** [CONTACT US](#)

⊖ 1 ⊕

A\$5,216.00

ADD TO CART

Qty 1+
A\$5,216.00

Volume Pricing
Request Quote

Get Product Downloads

Active Area Diameter (mm):
35

Connector:
USB

Model Number:
J-50MB-YAG
Coherent Part Number: 1191437

Type:
Meterless

Type of Sensor: Pyroelectric
Length of Cable (m): 3.0
Linearity (%): ±3
Calibration Uncertainty (%): ±2
Calibration Wavelength (nm): 1064
Noise Equivalent Energy (μJ): <240
Maximum Repetition Rate (pps): 50
Maximum Incident Beam Power (W): 20
Maximum Pulse Width (μs): 340
Wavelength Range (nm): 266 - 2100
Maximum Incident Energy Density: 14J/cm ² (10ns, 1064nm) 2.8J/cm ² (10ns, 532nm) 0.75J/cm ² (10ns, 355nm) 1.0J/cm ² (10ns, 266nm)
Energy Range: 2.4mJ - 3J

Regulatory Compliance

RoHS 2015: Exempt
Reach 224: Contains SVHC(s)
Certificate of Conformance: View