

JAI Go-X, 2402M-USB, 1/2.3" 2.3MP, USB Monochrom Camera



Stock #29-154 **1 In Stock**

⊖ 1 ⊕ A\$1,120⁰⁰

ADD TO CART

Volume Pricing

Qty 1+	A\$1,120.00 each
Need More?	Request Quote

Product Downloads

Monochrome

Spectrum:

General

Monochrome Camera

Type:

GOX-2402M-USB

Model Number:

JAI

Manufacturer:

Go-X

Camera Series:

Physical & Mechanical Properties

29 x 29 x 51.5
Dimensions (mm):

65
Weight (g):

Full
Housing:

Sensor

1/2.3"
Sensor Format:

2.30
Resolution (Megapixels):

162.00
Frame Rate (fps):

1,920 x 1,200
Pixels (H x V):

3.45 x 3.45
Pixel Size, H x V (µm):

6.6 x 4.1
Sensing Area, H x V (mm):

Sony IMX392
Imaging Sensor:

Progressive Scan CMOS
Type of Sensor:

Global
Shutter Type:

8/10/12 Bit
Pixel Depth:

USB3 Vision
Machine Vision Standard:

Electrical

4.3
Power Consumption (W):

Hardware & Interface Connectivity

USB 3.1 Gen 1
Interface:

USB 3.1 Gen 1, Micro-B
Connector:

Power Supply:
Power Supply Required and Sold Separately.
USA: #29-171
Europe: #29-171
Japan: #29-171
Korea: Not Available
China: Not Available

Hardware Trigger (GPIO) or Software Trigger
Synchronization:

Back Panel
Interface Port Orientation:

6-pin Hirose
GPIO Connector Type:

Threading & Mounting

C-Mount
Mount:

Environmental & Durability Factors

-5 to +45
Operating Temperature (°C):

-25 to +60
Storage Temperature (°C):

Regulatory Compliance

[View](#)
Certificate of Conformance:

Product Details

- Up to 12.3 MP Resolution
- USB and GigE Versions Available
- Longest Industry Warranty (6 Years)

JAI® Go-X Series Cameras are designed to be compact, industrial grade, reliable cameras with excellent image quality. Featuring industrial grade shock and vibration ratings (80G/10G) as well as excellent thermal dissipation, these

cameras are ideal for factory floors and assembly lines. Designed with a variety of capabilities, these cameras are capable of region-of-interest (ROI), blemish compensation with shading correction, and 8, 10, and 12-bit output. JAI® Go-X Series Cameras are available in resolutions ranging from 2.3 to 12.3MP with both USB or Gigabit Ethernet (GigE) outputs. Downloadable software is [available](#) for both GigE and USB options.

;