

[See all 65 Products in Family](#)

# IDS Imaging U3-3046LE-C-HQ 1/2.9" Color USB3 Camera (Recertified 05-P)

See More by [IDS Imaging Development Systems](#)



IDS Imaging uEye LE/XLE Camera (M12, Full Housing, Front View)



Stock #24-105-RCD-05P RECERTIFIED **1 In Stock**

[Similar Cameras](#)

A\$672.<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1+	A\$672.00 each
Need More?	<a href="#">Request Quote</a>

Product Downloads

Color Spectrum:

**General**

Color Camera Type:

U3-3046LE-C-HQ Rev.1.2 Model Number:

IDS Imaging Development Systems **Manufacturer:**

uEye LE **Camera Series:**

## Physical & Mechanical Properties

47 x 46 x 25 (excludes connectors and lens mount) **Dimensions (mm):**

38 **Weight (g):**

Full **Housing:**

## Sensor

Not Specified **Image Buffer:**

1/2.9" **Sensor Format:**

1.58 **Resolution (Megapixels):**

230.00 **Frame Rate (fps):**

1,456 x 1,088 **Pixels (H x V):**

3.45 x 3.45 **Pixel Size, H x V (µm):**

5.03 x 3.75 **Sensing Area, H x V (mm):**

Sony IMX273 **Imaging Sensor:**

Progressive Scan CMOS **Type of Sensor:**

Global **Shutter Type:**

12 bit **Pixel Depth:**

40µs - 2s **Exposure Time:**

Not Specified **Dynamic Range (dB):**

USB3 Vision v1.1 **Machine Vision Standard:**

## Electrical

1 - 2 **Power Consumption (W):**

## Hardware & Interface Connectivity

USB 3.0 **Interface:**

USB Type-C **Connector:**

Power over USB **Power Supply:**

N/A **GPIOs:**

Hardware Trigger (GPIO); Software Trigger **Synchronization:**

Back Panel (Right Angle) **Interface Port Orientation:**

N/A **GPIO Connector Type:**

## Threading & Mounting

S-Mount (M12 x 0.5) **Mount:**

1/4-20 with Tripod Mount Adapter [#16-017](#) **Mounting Threads:**

## Environmental & Durability Factors

0 to +55 **Operating Temperature (°C):**

-20 to +80 **Storage Temperature (°C):**

## Regulatory Compliance

[Exempt](#) **RoHS 2015:**

[View](#) **Certificate of Conformance:**

[Contains SVHC\(s\)](#) **REACH 241:**

## Product Details

- Up to 8.0MP Resolution with Framrates up to 230fps
- Board Level Options with C/CS-Mbunt or S-Mbunt Available
- GenICam USB3 Vision Compliant

IDS Imaging uEye LE/XLE USB3.1 Cameras utilize [IDS Imaging's peak SDK platform](#) that supports GeniCam and USB3 Vision standards for ease of software development and integration. These cameras are available in board-level or housed options with S-Mbunt or C/CS-Mbunt versions. The C/CS-Mbunt configurations come with a 5mm spacer to easily adapt between C-Mbunt and CS-Mbunt lenses. IDS Imaging uEye LE/XLE USB3.1 Cameras are ideal for small device construction, medical technology, robotics, and machine vision applications. With a compact design, the XLE version is suitable for integration into embedded systems whereas the LE version is suitable for small device projects.

;