

Laminated Wratten ND Filter 2.0 OD 25mm Dia



Stock #29-317 20+ In Stock

-

1

+

A\$160^{.00}

ADD TO CART

Volume Pricing	
Qty 1-10	A\$160.00 each
Qty 11-25	A\$129.60 each
Need More?	Request Quote

Product Downloads

General

Type:

Neutral Density Filter

Note:

Supplied with protective film on both sides

Physical & Mechanical Properties

Diameter (mm):

25.00 +/- 0.25

Optical Properties

Optical Density OD (Average):	
2	
Substrate: ☐	
Wratten 2 Filter, One-Side Laminated onto PMMA	
Coating:	
Uncoated	
Blocking Wavelength Range (nm):	
400-700	
Regulatory Compliance	
Certificate of Conformance:	
View	

Product Details

- One-Side Laminated for Stability
 - Available in 25mm and 48mm Sizes
 - Kodak Filter No. 96
 - Lightweight Alternative to Traditional Glass ND Filters
- PMMA-Laminated Wratten ND Filters are ideal for light attenuation in image-forming optical systems to reduce light intensity across the visible spectrum without altering the spectral profile. The laminated design offers additional stability and durability compared to traditional polyester/gelatin filters while remaining a lightweight alternative to traditional glass ND filters. These ND filters are available in 25mm or 48mm diameters and a thickness of 0.6mm. PMMA-Laminated Wratten ND Filters are uncoated and feature a blocking wavelength of 400 - 700nm with OD options of 0.1, 0.3, 0.5, 1.0, 2.0, and 3.0.