

Coherent® LightSmyth™ 1030nm, 1600 Grooves/mm, 31.8 x 12.3mm Transmission Diffraction Grating

See More by [Coherent®](#)



LightSmyth™ Transmission Diffraction Gratings

Stock #16-863 3-5 DAYS

- 1 + **A\$984.00**

ADD TO CART

Qty 1+
A\$984.00
Volume Pricing
Request Quote

Get Product Downloads



Groove Density (grooves/mm): 1600
Groove Density Uniformity (grooves/mm): 0.001
Design Wavelength DWL (nm): 1030 ±10

Minimum Efficiency (%) : ≥94 @ 1030nm
Dimensions (mm) : 31.80 x 12.30
Angle of Incidence (°) : 55.5 ±1
Clear Aperture CA (mm) : 30.80 x 11.30
Coating : Dielectric
Construction : Multi-Layer Dielectric Binary Etch Grating
Length (mm) : 31.80
Model Number : 1304192
Substrate :  Fused Silica (Corning 7980)
Surface Quality : 60-40
Thickness (mm) : 0.95 ±0.050
Type : Transmission Diffraction Grating
Width (mm) : 12.30
Alignment of Grooves to Edge (°) : 0.1 (typical)
Polarization : S
Note : S-Polarization defined with E-field parallel to the grating grooves

Regulatory Compliance

RoHS : Compliant
Certificate of Conformance : View