

LUCID Vision Labs Atlas10 ATX081S-CC, Sony IMX536, 8.1MP, Color Camera

See More by [LUCID Vision Labs™](#)



LUCID Vision Labs Atlas10 10GigE Power over Ethernet (PoE) Cameras (Front, C-Mount)



Stock **#18-475** 3-5 DAYS

⊖ 1 ⊕

A\$3,811.20

ADD TO CART

Qty 1+
A\$3,811.20
Volume Pricing
Request Quote

Get Product Downloads

Video Output:
10GigE (PoE+)

Type:
Color Camera

Manufacturer:
Lucid Vision Labs

Mounting Threads:

2 x ¼-20 with Tripod Mount Adapter [#17-120](#)

Image Buffer: 380MB
Camera Family: Atlas10
Model Number: ATX081S-CC
Imaging Sensor: Sony IMX536
Type of Sensor: Progressive Scan CMOS
Type of Shutter: Global
Camera Sensor Format: 2/3"
Resolution (MegaPixels): 8.10
Pixels (H x V): 2,840 x 2,840
Pixel Size, H x V (µm): 2.74 x 2.74
Sensing Area, H x V (mm): 7.78 x 7.78
Frame Rate (fps): 136.70
Pixel Depth: 8/10/12 bit
Exposure Time: 5.05µs - 10s
Connector: 10GigE, M12
Power Supply: Power Supply Required and Sold Separately. USA: #18-364 Europe: #18-364 Japan: #18-364 Korea: Not Available China: #18-364
Power Consumption (W): 11.5 (External Power Supply) <12 (PoE+)
GPIOs: 1 opto-isolated input, 1 opto-isolated output, 2 non-isolated bi-directional ports
Synchronization: Hardware Trigger (GPIO), Software Trigger, or PTP (IEEE 1588)
Dimensions (mm): 55 x 55 x 95.5 (excludes connectors and lens mount)
Weight (g): 304
Mount: C-Mount
Housing: Full
Interface Port Orientation: Back Panel
Operating Temperature (°C): -20 to +55
Storage Temperature (°C): -30 to +60
GPIO Connector Type: 8-pin M8
Machine Vision Standard: GigE Vision v2.0

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View