

## $\lambda/2$ 735-985nm, Polymer Achromatic Retarder



Stock #49-229 **1 In Stock**

⊖ 1 ⊕ A\$2,000<sup>00</sup>

**ADD TO CART**

### Volume Pricing

Qty 1-5	A\$2,000.00 each
Qty 6+	A\$1,776.00 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

### General

Achromatic Waveplate **Type:**

### Physical & Mechanical Properties

10.16 **Clear Aperture CA (mm):**

25.40 **Diameter (mm):**

6.35 ±0.508 **Thickness (mm):**

±0.127 **Dimensional Tolerance (mm):**

Birefringent Polymer Stack **Construction:**

## Optical Properties

**N-BK7** **Substrate:**

0.5 **Reflection (%):**

$\lambda/2$  **Retardance:**

40-20 **Surface Quality:**

$\lambda/4$  @ 632.8nm **Transmitted Wavefront, P-V:**

$\lambda/100$  **Retardance Tolerance:**

1.00 **Beam Deviation (arcmin):**

735 - 985 **Wavelength Range (nm):**

500 W/cm<sup>2</sup> **Damage Threshold, By Design:**

## Threading & Mounting

6.35 **Mount Thickness (mm):**

## Environmental & Durability Factors

-20 to +50 **Operating Temperature (°C):**

## Regulatory Compliance

**Compliant** **RoHS 2015:**

**View** **Certificate of Conformance:**

**Compliant** **REACH 241:**

## Product Details

- Broad Spectral Range
- $\lambda/100$  Retardance Accuracy
- $\lambda/4$  and  $\lambda/2$  Retardance
- High Damage Threshold of 500 W/cm<sup>2</sup>

Precision Achromatic Waveplates (Retarders) consist of a polymer stack layered between two precision BK7 windows, and are available in standard  $\lambda/4$  and  $\lambda/2$  options for common visible and NIR wavelengths. These waveplates (retarders) will experience less than 1% retardance change over a  $\pm 10^\circ$  angle of incidence. Each Precision Achromatic Waveplates (Retarders) is mounted in a metal ring with the fast axis clearly marked.

## Technical Information

