

M105 x 1.00 Mounted Linear Glass Polarizing Filter



Mounted Linear Glass Polarizing Filters

Stock **#64-903** CLEARANCE **20+ In Stock**

-

1

+

A\$300⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	A\$300.80 each
Need More?	Request Quote

Product Downloads

General	
Mounted Imaging Filter	Type:
Physical & Mechanical Properties	
99.00	Clear Aperture CA (mm):
110.00 +0/-0.2	Diameter (mm):
Dichroic	Construction:

Optical Properties	
Uncoated	Coating:
Approx. 19:1 at 400nm Approx. 200:1 at 500nm ≥2700:1 at 550-650nm Approx. 600:1 at 700nm	Extinction Ratio:
Float Glass	Substrate: □
95% Efficiency	Polarization:
Single: 30 Crossed: 0.15	Transmission (%):
400 - 700	Wavelength Range (nm):
Threading & Mounting	
M105 x 1.00	Filter Thread:
9 ±0.1	Mount Thickness (mm):
11	Mount Thickness Including Threads (mm):
Environmental & Durability Factors	
-15 to +70	Operating Temperature (°C):
Regulatory Compliance	
View	Certificate of Conformance:

Product Details

- Stackable, Rotating Mount for Easy Integration into Imaging Systems
- Eliminate Hot Spots and Reduce Glare
- 95% Polarization Efficiency
- Also Available [Unmounted](#)

Mounted Linear Glass Polarizing Filters feature a rotatable threaded mount available in a wide range of standard thread sizes. Linear polarizing filters will transmit a single axis of polarization and can be used to reduce glare and hot spots in imaging systems. Two polarizing filters can be stacked to achieve a variable density effect. Thickness includes a 2mm male thread. Mounted Linear Glass Polarizing Filters have 95% polarization efficiency. The filters are also available [unmounted](#).

Technical Information

