

[See all 13 Products in Family](#)

## M52 x 0.75 Mounted Linear Glass Polarizing Filter



Mounted Linear Glass Polarizing Filters

Stock #25-086 **1 In Stock**

- 1 + A\$106<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1-9	A\$106.40 each
Qty 10-25	A\$101.60 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

### General

Mounted Imaging Filter **Type:**

### Physical & Mechanical Properties

47.50 **Clear Aperture CA (mm):**

54.60 **Diameter (mm):**

**Construction:**

## Optical Properties

Uncoated **Coating:**

Extinction Ratio:  
 Approx. 19:1 at 400nm  
 Approx. 200:1 at 500nm  
 ≥2700:1 at 550-650nm  
 Approx. 600:1 at 700nm

Float Glass **Substrate:** □

95% Efficiency **Polarization:**

Single: 30 **Transmission (%):**  
 Crossed: 0.15

400 - 700 **Wavelength Range (nm):**

## Threading & Mounting

M52 x 0.75 **Filter Thread:**

6.80 **Mount Thickness (mm):**

## Environmental & Durability Factors

-15 to +70 **Operating Temperature (°C):**

## Regulatory Compliance

[View](#) **Certificate of Conformance:**

## Product Details

- Stackable, Rotating Mount for Easy Integration into Imaging Systems
- Eliminate Hot Spots and Reduce Glare
- 95% Polarization Efficiency
- Also Available [Unmounted](#)

Mounted Linear Glass Polarizing Filters feature a rotatable threaded mount available in a wide range of standard thread sizes. Linear polarizing filters will transmit a single axis of polarization and can be used to reduce glare and hot spots in imaging systems. Two polarizing filters can be stacked to achieve a variable density effect. Thickness includes a 2mm male thread. Mounted Linear Glass Polarizing Filters have 95% polarization efficiency. The filters are also available [unmounted](#).

## Technical Information

