

Lightpath 7100341 | 20mm FL, f/1.2, Thermal Imaging Lens Assembly

See More by [Lightpath®](#)



Stock #15-692 CLEARANCE 3-5 DAYS

-

1

+

A\$278.32

ADD TO CART

Qty 1+

A\$278.32

Volume Pricing

[Request Quote](#)

Get Product Downloads

Effective Focal Length EFL (mm):
20.00

Substrate: ☐
Black Diamond™ BD-6

f/#:
1.2

Coating:
BBAR (8000-12000nm)

Wavelength Range (nm):
8000 - 12000

Clear Aperture CA (mm): 17.00
Coating Specification: R _{avg} <0.75% @ 8000 - 12,000nm
Coefficient of Thermal Expansion CTE (10⁻⁶/°C): 22.5
Compatible Window: Thickness: 0.70mm Material: Si
Construction: Matte Black Anodized Aluminum Housing
Index of Refraction n_d @ 10µm: 2.7816
Index of Refraction n_d @ 14µm: 2.7683
Index of Refraction n_d @ 4µm: 2.7978
Length (mm): 21.42
Lightpath Lens Code: 7100341
Mounting Threads: M19 x 0.5
Thermo-optic coefficient dn/dT: 30.5 x 10 ⁻⁶ @ 10µm
Working Distance (mm): 7.96
Front Diameter (mm): 25.40
Thread Length (mm): 6.50
Recommended Detector Format (H x V/Pixel Size): 640 x 512 / 10µm

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant