

**TECHSPEC® Near Infrared Plate Beamsplitter Kit, 25mm Diameter**



Stock #83-956 **1 In Stock**

⊖ 1 ⊕ A\$864.<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1+	A\$864.00 each
Need More?	<a href="#">Request Quote</a>

Product Downloads

**General**

**Note:**  
Beamsplitter-coated side is marked with a black dot

**Number of Filters:**  
5: [#47-242](#), [#68-386](#), [#45-853](#), [#68-404](#), [#48-399](#)

**Type:**  
Standard Beamsplitter

**Physical & Mechanical Properties**

**Construction:**  
Plate

## Optical Properties

### Coating Specification:

Surface 1: R/T  $\pm 5\%$  @ 900nm,  $R_{avg} \pm 10\%$  700 - 1100nm  
Surface 2: AR  $R_{avg} \leq 1\%$ ,  $R_{avg} \leq 2\%$  700 - 1100nm

### Wavelength Range (nm):

700 - 1100

## Regulatory Compliance

### Certificate of Conformance:

[View](#)

## Product Details

- Many Beamsplitting Ratios Available
- Visible and NIR Coating Options Offered
- Multi-Layer AR Coated Second Surface
- [C-Mounted Plate Beamsplitters](#) Also Available

TECHSPEC® Visible and NIR Plate Beamsplitters are ideal for dual magnification [imaging](#) systems and for combining low power [laser](#) beams. These beamsplitters offer the optimum combination of polished, high-quality optical-grade glass with minimum substrate thickness. The broadband dielectric coatings provide maximum throughput, are ideal for minimizing ghost images, and have much less energy loss than metallic coatings. TECHSPEC® Visible and NIR Plate Beamsplitters are coated on their back surfaces with a multi-layer anti-reflection (AR) coating, reducing back reflections to less than 1.0% for each wavelength range. Note that for easy identification, the coated side of the beamsplitter is marked with a black dot.

## Technical Information

