

Nikon 200mm Standard FOV Tube Lens

See More by [Nikon](#)



Stock **#75-377** NEW [CONTACT US](#)

-

1

+

A\$708⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	A\$708.80 each
Need More?	Request Quote

Product Downloads

General

Type:	Tube Lens
Manufacturer:	Nikon

Physical & Mechanical Properties

Length (mm):	28.00
Maximum Diameter (mm):	38

Optical Properties

Focal Length FL (mm):	200.00
-----------------------	--------


1x	Magnification:
380 - 1000	Wavelength Range (nm):
22 regularly, up to a maximum of 25	Field Number (mm):
33	Entrance Pupil Diameter (mm):
Threading & Mounting	
M38x0.5	Mounting Threads:
Regulatory Compliance	
View	Certificate of Conformance:

Product Details

• Superior UV Transmission
• High Numerical Aperture Designs
• Feature Low Auto-Fluorescence Materials

Nikon CFI Super Fluor Objectives are designed to provide superior transmission to ultraviolet applications operating down to 340nm, including for use with fluorochromes indo-1, fura-2, and fluo-3, or for photo-activation of caged compounds. Nikon CFI Super Fluor Objectives are designed using low auto-fluorescence materials along with high numerical apertures to guarantee sharp, bright fluorescence images. These microscope objectives have been optimized for improved signal-to-noise ratios at short wavelengths.

Technical Information



Dimensions (mm)						
Stock No.	Magnification	Parafocal Length	A	B	C	D
#88-374	4X	60.06	30.0	44.4	19.7	M25 x0
#88-375	10X	60.06	32.0	58.7	8.0	M25 x0
#88-376	20X	60.06	33.5	58.9	9.0	M25 x0
#88-377	40X	60.06	33.0	59.6	7.5	M25 x0