

Lumenera INFINITY5 5-5 Microscopy Monochrome Camera

See More by [Teledyne Lumenera](#)



Stock **#16-679** **1 In Stock**

-

1

+

A\$6,840⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	A\$6,840.00 each
Need More?	Request Quote

Product Downloads

Monochrome	Spectrum:
General	
Monochrome Microscopy Camera	Type:
INFINITY5-5M	Model Number:
Teledyne Lumenera	Manufacturer:

INFINITY	Camera Series:
Physical & Mechanical Properties	
97.8 x 69.8 x 50.8 (excludes lens mount)	Dimensions (mm):
330	Weight (g):
Full	Housing:
Sensor	
Not Specified	Image Buffer:
2/3"	Sensor Format:
5.10	Resolution (Megapixels):
75.00	Frame Rate (fps):
2,464 x 2,056	Pixels (H x V):
3.45 x 3.45	Pixel Size, H x V (µm):
8.5 x 7.09	Sensing Area, H x V (mm):
Sony IMX250	Imaging Sensor:
Progressive Scan CMOS	Type of Sensor:
Global	Shutter Type:
8/12 bit	Pixel Depth:
14µs - 14s (video)	Exposure Time:
72	Dynamic Range (dB):
2.30	Read Noise (e ⁻):
Electrical	
4	Power Consumption (W):
Hardware & Interface Connectivity	
USB 3.1 Gen 1 (HDMI)	Interface:
Power over USB	Power Supply:
Not Specified	GPIOs:
Hardware Trigger (GPIO)	Synchronization:
Side Panel	Interface Port Orientation:
8-pin Hirose (MRX)	GPIO Connector Type:
Threading & Mounting	
C-Mount	Mount:
2 x ¼-20 (Integrated into Housing)	Mounting Threads:
Environmental & Durability Factors	
0 to +50	Operating Temperature (°C):
-30 to +70	Storage Temperature (°C):
Regulatory Compliance	
View	Certificate of Conformance:

Product Details

- Ideal for Life Sciences, Clinical, and Industrial Applications
- USB or HDMI Video Output Options
- Powerful Capture and Analysis Software Included
- PC & Mac Compatibility



Teledyne Lumenera INFINITY5 Microscopy Cameras are an excellent fit for quantitative and low-light applications. These cameras are compatible with any c-mount, come complete with image analysis software and an industry leading four (4) year warranty. The CMOS models also have HDMI output, enabling direct video output to monitors with an HDMI port. Their high dynamic range and 14-bit output make these cameras a versatile entry-level research camera for documentation and image analysis in life science, clinical and material science applications. Teledyne Lumenera INFINITY Microscopy Cameras easily manage seconds of exposure time with a dark current rating of less than 1 e-/s and a low noise level comparable to sCMOS cameras.

These Teledyne Lumenera INFINITY5 Microscopy Cameras feature ultra-sensitive Sony sensors, and their performance and price make them an ideal solution for fluorescence applications. The cameras feature a unique noise reduction technology that includes high grade components, low noise electronics and improved thermal management techniques.

Note: The INFINITY3 & INFINITY2 Series have been discontinued by the manufacturer but are still available for purchase in limited quantities.