

[See all 59 Products in Family](#)

Coherent® OBIS™ 1230933 | 488nm LS 80mW Laser

See More by [Coherent®](#)



Stock **#88-024** [CONTACT US](#)

-

1

+

A\$12,000^{.00}

ADD TO CART

Volume Pricing	
Qty 1+	A\$12,000.00 each
Need More?	Request Quote

Note: This item requires accessories for use | [Learn More](#)

Product Downloads



General

Warm-Up Time (minutes):
<5

Manufacturer:
Coherent®

Type of Laser:
Diode

IIIb	Laser Class - CDRH:	
1230933	Model Number:	
Physical & Mechanical Properties		
<5	Pointing Stability (μrad/°C):	
<30	Pointing Stability (μrad):	
Optical Properties		
100:1	Polarization:	
TEM ₀₀	Spatial Mode:	
488.00 ±2	Wavelength (nm):	
≤1.1	Mode Quality, M²:	
±0.05	Beam Diameter Tolerance (mm):	
0.7	Beam Diameter (mm):	
<1.2	Beam Divergence (mrad):	
Blue	Color:	
Electrical		
80	Output Power (mW):	
<2	Power Stability (%):	
Digital: 0.05	Modulation Frequency (MHz):	
Analog: 100	Modulation Frequency (kHz):	
≤0.25% (20Hz to 20MHz)	RMS Noise:	
Hardware & Interface Connectivity		
Power Supply:		
Power Supply Required and Sold Separately.		
USA: #87-473		
Europe: #87-473		
Japan: #87-473		
Korea: #87-473		
China: #87-473		
Output Type:		
Free Space		
Environmental & Durability Factors		
15 to 40	Operating Temperature (°C):	
Regulatory Compliance		
Exempt	RoHS 2015:	
Contains SVHC(s)	Reach 224:	
View	Certificate of Conformance:	

Product Details

- Same Compact Design for All Wavelength Options
- Integrated Control Electronics with Analog and Digital Modulation
- Circular Beam with Superior Beam Quality
- [Coherent® High Performance OBIS™ LX/LS Fiber-Pigtailed Laser Systems](#) Also Available

Coherent® High Performance OBIS™ LX/LS Laser Systems are compact, plug-and-play lasers that offer a wide range of wavelengths from the ultraviolet to the near-infrared in a single platform. Although each laser utilizes one of two technologies, either Coherent's proprietary Optically Pumped Semiconductor Laser (OPSL) or laser diode-based, these laser systems feature the same beam parameters in packages that allow the user to plug-and-play alternate wavelengths as needed. Coherent® High Performance OBIS™ LX/LS Laser Systems includes a USB, RS-485, and full I/O interface. A multicolor LED has been integrated into the top cover to provide laser status at a glance.

OBIS Laser System Startup Guide

This downloadable PDF provides guidance on interfacing with OBIS controllers and power supplies, mounting and connecting the heatsink, and starting modulation.

[Download Startup Guide](#)

Note: A power supply is required for operation and sold separately. OBIS remote is required for CDRH certified systems. The OBIS heat sink is recommended.

Three power supply options are available, but only one is required. [#87-472](#) (not CDRH certified) includes a power supply with power cord. [#87-473](#) (CDRH certified) includes a 1m laser-to-remote cable, and DC power supply with power cable. [#87-475](#) (CDRH certified) includes a 6 laser scientific remote, internal power supply, and six 1m laser-to-remote cables with power cord.

Coherent® High Performance OBIS™ LXLS Laser Systems are designed for an extensive range of OEM or scientific applications including environmental monitoring, inspection, or machine vision, or for use in the life sciences for the fluorescence excitation of dyes and proteins in flow cytometry, microscopy, DNA sequencing, polymerase chain reaction (PCR) diagnostic instruments, or drug delivery. These lasers feature smart electronics to ensure superior low-noise optical performance, and an ultra-small controller that has been integrated into the laser head.

Technical Information

