

[See all 6 Products in Family](#)

OCT Pyramid phantom, negative, step size 40um



Stock **#71-283** **1 In Stock**

-

1

+

A\$1,400^{.00}

ADD TO CART

Volume Pricing	
Qty 1-4	A\$1,400.00 each
Qty 5-9	A\$1,260.00 each
Need More?	Request Quote

Product Downloads

General

Pyrimid Phantom

Type:

Physical & Mechanical Properties

20 x20

Dimensions (mm):

50µm

Step Thickness:

40µm

Step Size:

Regulatory Compliance

[View](#)

Certificate of Conformance:

Product Details

- Point Spread, Multilayer, Pyramid, and Multipurpose Phantoms Available
- Positive and Negative Target Options
- Ideal for Calibration of OCT Devices

Optical Coherence Tomography (OCT) Phantoms provide a controlled sample to test and calibrate OCT systems, ensuring accuracy and reliability of measurements. These homogeneous phantoms with well characterized optical properties, are available in Point Spread, Multilayer, Pyramid, and Multipurpose designs, offering a range of OCT calibration options. Additionally, these phantoms enable validation of image processing algorithms and quality assurance protocols providing consistency in clinical and research settings. Optical Coherence Tomography (OCT) Phantoms are ideal for testing 3D spatial depth resolution of OCT imaging devices as well as testing image processing software and algorithms

- Point Spread: 3D distribution of <1µm FeO nanoparticles encased in polymer.
- Multilayer: Multilayers of 50µm thickness, mimicking a tissue with known optical properties.
- Pyramid: Pyramid shape with 40um steps and 50um step depth, available as positive or negative.
- Multipurpose: USAF, alignment crosswire, aperture, point spread function, and an annotated Ronchi ruler targets.