

Olympus LMPLN10XIR 10X NIR Objective

See More by [Olympus](#)



Olympus LMPLN10XIR 10XNIR Objective

Stock **#90-481** NEW **1 In Stock**

-

1

+

A\$7,736^{.00}

ADD TO CART

Volume Pricing	
Qty 1+	A\$7,736.00 each
Need More?	Request Quote

Product Downloads

SPECIFICATIONS

General

LMPLN10XIR

Model Number:

Compatible Tube Lens Focal Length (mm):
Focal Length: 180mm

Type:


Microscope Objective	
Infinity Corrected	Style:
Olympus	Manufacturer:
Physical & Mechanical Properties	
2.20	Field of View (mm):
27.05	Length excluding Threads (mm):
26.00	Maximum Diameter (mm):
78	Weight (g):
Optical Properties	
N/A	Compatible Cover Glass Thickness (mm):
18.00	Focal Length FL (mm):
10X	Magnification:
0.30	Numerical Aperture NA:
1.12	Resolving Power (μm):
3.05	Depth of Field (μm):
18.00	Working Distance (mm):
400 - 1600	Wavelength Range (nm):
22	Field Number (mm):
45	Parfocal Length (mm):
N/A	Immersion Liquid:
Threading & Mounting	
RMS / 20.32mm x 36 TPI	Mounting Threads:
Regulatory Compliance	
View	Certificate of Conformance:

PRODUCT DETAILS

- Long Working Distances to Reduce Risk of Specimen Damage
- Correction Collars to Adjust for Specimen Thickness
- Ideal for Silicon Wafer Inspection

Olympus Plan Achromatic Near-Infrared Objectives provide high transmission between 700 - 1600nm, making them an excellent choice for near-infrared microscopy when coupled with an NIR tube lens. These objectives feature long working distances to reduce the risk of damage to specimens and support up to field number 22 for observation. Magnifications of 20X and higher feature a correction collar to correct for aberrations based on the thickness of either the glass or silicon substrate being inspected. Olympus Plan Achromatic Near-Infrared Objectives are ideal for use in silicon wafer inspection to view the internal structure for defects.

TECHNICAL INFORMATION



LMPLN10XIR Transmission Graph