


[See all 4 Products in Family](#)

Multi-Grid Standard Stage Micrometer on Opal Glass



Stock **#59-278** [CONTACT US](#)

-

1

+

A\$1,000^{.00}

ADD TO CART

Volume Pricing	
Qty 1-4	A\$1,000.00 each
Qty 5+	A\$951.52 each
Need More?	Request Quote

Product Downloads

General

NIST Certification:

No

Physical & Mechanical Properties

Scale Divisions:

0.5mm (25µm divisions), 1.0mm (50µm divisions),
2.0mm (100µm divisions), 4.0mm (200µm
divisions), angle grid (15° segments)

Dimensions (mm):

25.4 x 76.2

	Thickness (mm):
1.50 ±0.100	
	Dimensional Tolerance (mm):
±0.100	

Optical Properties

	Substrate:
Chrome on Opal Glass	

Regulatory Compliance

	RoHS 2015:
Compliant	
	Certificate of Conformance:
View	
	Reach 235:
Compliant	

Product Details

- Calibrate Distortion in High Magnification Systems
- The Multi-Grid Stage Micrometer features grids of varying frequency, and is ideal for calibrating distortion in microscopic systems. Grid sizes are 0.5mm (25µm divisions), 1.0mm (50µm divisions), 2.0mm (100µm divisions) and 4.0mm (200µm divisions). Micrometer also features an angle grid (15° segments). Target is chrome on glass, 1" x 3" x 1.5mm.