


[See all 2 Products in Family](#)

Negative 1" x 3", Dot and Square Calibration Target



Negative 1" x 3", #62-269

Stock **#62-269** CLEARANCE **1 In Stock**

-

1

+

A\$1,032⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-4	A\$1,032.00 each
Qty 5+	A\$981.44 each
Need More?	Request Quote

Product Downloads

General

Negative Target	Type:
Included	NIST Certification:

Physical & Mechanical Properties

±0.02	Dimensional Tolerance (inches):
	Dimensions (inches):

1 x3	
0.060	Thickness (inches):
±0.001	Thickness Tolerance (inches):
0.005	Parallelism (inches):
Optical Properties	
Float Glass	Substrate:
20-10	Surface Quality:
<4λ	Surface Flatness (P-V):
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 240:

Product Details

- Designed for Measurement Calibration
- Positive or Negative Chrome Patterns on Glass
- High Contrast Target for Imaging with Elements from 0.5 to 10mm
- NIST Traceability Certificate Included

These targets provide a highly accurate reference for feature sizes of circles and squares and are ideal for testing the accuracy of non-contact metrology systems, especially those vulnerable to distortion and blooming. The precision pattern is formed in Low Reflection Chromium on a stable Float Glass substrate in standard microscope slide format. The low reflection pattern surface provides high contrast against a light background, ideal for diffuse or coaxial illumination applications. The pattern is applied to the first surface and features both circles and squares in 0.5mm and whole-number-sized increments from 1mm to 10mm. The Positive Target features an opaque pattern on a clear background, whereas the Negative Target features a clear pattern on an opaque background.