

## NTX Tube (2X)



#86-892: NTXTube (2X)

Stock **#86-892** [CONTACT US](#)

⊖ 1 ⊕ **A\$944<sup>00</sup>**

**ADD TO CART**

### Volume Pricing

|            |                               |
|------------|-------------------------------|
| Qty 1+     | <b>A\$944.00</b> each         |
| Need More? | <a href="#">Request Quote</a> |

### Product Downloads

### General

Lens Accessory **Type:**

### Regulatory Compliance

[Compliant](#) **RoHS 2015:**

[Compliant](#) **Reach 224:**

[View](#) **Certificate of Conformance:**

## Product Details

- CentriTel® Internal Focusing System for Constant Magnification
- Focuses from 3000mm to 60mm with MX-Series Objectives
- Can be Equipped with Infinity-corrected Microscope Objectives
- Coaxial In-line Illuminator (Optional) for Reflective Objects

CentriMax™ can be actively focused anywhere from 3000mm to 60mm by using supplemental MX-Series objectives. Once a working distance is chosen, its patented CentriTel® internal focusing system allows for focusing from top to bottom of objects without change in magnification. Unlike InfiniMax™, CentriMax™ does not need physical movement to maintain magnification by a resetting of the focus. Rather, the CentriTel® internal focusing system maintains constant magnification during focal translation. Depth details peel away, yet magnification remains essentially constant. CentriMax™ is perfect for z-sectioning and making measurements from a fixed position. This lens also features a variable iris diaphragm for increased depth of field without altering CentriTel® characteristics. Other accessories include: supplemental adapters (transmitted or coaxial) for use with Achrovid™, Mutoyo, Edmund, Olympus, or Nikon infinity corrected objectives.

## Technical Information

| Objective       | Working Distance | Magnification | Field of View, FOV |
|-----------------|------------------|---------------|--------------------|
| MX-LR (#86-894) | 3000mm           | 0.11X         | 7.0mm              |
|                 | 1330mm           | 0.25X         | 8.1mm              |
|                 | 530mm            | 0.58X         | 14.0mm             |
| MX-1 (#56-014)  | 310mm            | 0.96X         | 7.0mm              |
|                 | 400mm            | 0.83X         | 8.1mm              |
|                 | 690mm            | 0.48X         | 14.0mm             |
| MX-2 (#56-015)  | 240mm            | 1.22X         | 5.5mm              |
|                 | 295mm            | 1.12X         | 6.0mm              |
|                 | 425mm            | 0.74X         | 9.0mm              |
| MX-3 (#56-016)  | 175mm            | 1.76X         | 3.8mm              |
|                 | 218mm            | 1.49X         | 4.5mm              |
|                 | 273mm            | 1.12X         | 6.0mm              |
| MX-4 (#56-017)  | 165mm            | 1.91X         | 3.5mm              |
|                 | 190mm            | 1.68X         | 4.0mm              |
|                 | 238mm            | 1.34X         | 5.0mm              |
| MX-5 (#56-018)  | 130mm            | 2.23X         | 3.0mm              |
|                 | 145mm            | 2.09X         | 3.2mm              |
|                 | 175mm            | 1.68X         | 4.0mm              |
| MX-6 (#56-019)  | 60mm             | 4.47X         | 1.5mm              |
|                 | 65mm             | 4.47X         | 1.5mm              |
|                 | 70mm             | 4.19X         | 1.6mm              |