

[See all 12 Products in Family](#)

Polarization Maintaining High ER Patchcord, FC/APC, 0.12NA, 1270-1625nm, 1m



FC/APC Connector

Stock **#25-993** **4 In Stock**

⊖ 1 ⊕ A\$440⁰⁰

ADD TO CART

Volume Pricing

Qty 1-4	A\$440.00 each
Qty 5-24	A\$396.80 each
Need More?	Request Quote

Product Downloads

General

PM1300-XP **Fiber Cable Type:**

Aligned to Connector Key **Slow Axis Alignment:**

Physical & Mechanical Properties

1 +0.1/-0.0 **Length (m):**

Jacket Material:

2mm Narrow Key **Key Width:**

Optical Properties

0.12 **Numerical Aperture NA:**

1310 **Alignment Wavelength (nm):**

1270 - 1625 **Wavelength Range (nm):**

9.3 ± 0.5µm @ 1300nm **Mode Field Diameter (nm):**

30dB (Min)
33dB (Typ.) **Extinction Ratio:**

Hardware & Interface Connectivity

FC/APC **Connector:**

0.30dB (Max)
0.20dB (Typ.) **Insertion Loss (dB):**

60 **Loss (dB):**

Environmental & Durability Factors

0 to 70 **Operating Temperature (°C):**

-45 to 85 **Storage Temperature (°C):**

Regulatory Compliance

Compliant **RoHS 2015:**

View **Certificate of Conformance:**

Compliant **REACH 241:**

Product Details

- FC/PC, FC/APC, or Hybrid Terminated Connectors
- Patchcords for Wavelengths from 970 – 1625nm
- Extinction Ratios up to 33 dB
- Ideal for Use with 980, 1064, 1310, and 1550nm IR Lasers

High Extinction Ratio Polarization Maintaining Fiber Optic Patchcords are available with FC/PC or FC/APC terminated connectors. Hybrid terminated connectors enable users to adapt FC/PC and FC/APC patchcords for compatibility with existing fiber assemblies. When used at the fiber specific alignment wavelength, these fiber patchcords provide extinction ratios between 30 – 33 dB to better maintain input polarization. High Extinction Ratio Polarization Maintaining Fiber Optic Patchcords are ideal for applications including telecommunications, interferometry, and quantum key distribution. Each connector is engraved with the fiber type for easy integration and identification.

Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).