

[See all 2 Products in Family](#)

Positive 1" x 3", Dot and Square Calibration Target



Positive 1" x3", #62-268

Stock **#62-268** [CONTACT US](#)

-

1

+

A\$1,032⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-4	A\$1,032.00 each
Qty 5+	A\$981.44 each
Need More?	Request Quote

Product Downloads

General

	Type:
Positive Target	
	NIST Certification:
Included	

Physical & Mechanical Properties

	Dimensional Tolerance (inches):
±0.02	
	Pattern Size (mm):

0.5 to 10	
1 x3	Dimensions (inches):
0.060	Thickness (inches):
±0.001	Thickness Tolerance (inches):
0.005	Parallelism (inches):
±2.5	Pattern Tolerance (µm):

Optical Properties	
Float Glass	Substrate:
20-10	Surface Quality:
<4λ	Surface Flatness (P-V):

Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 240:

Product Details

- Designed for Measurement Calibration
- Positive or Negative Chrome Patterns on Glass
- High Contrast Target for Imaging with Elements from 0.5 to 10mm
- NIST Traceability Certificate Included

These targets provide a highly accurate reference for feature sizes of circles and squares and are ideal for testing the accuracy of non-contact metrology systems, especially those vulnerable to distortion and blooming. The precision pattern is formed in Low Reflection Chromium on a stable Float Glass substrate in standard microscope slide format. The low reflection pattern surface provides high contrast against a light background, ideal for diffuse or coaxial illumination applications. The pattern is applied to the first surface and features both circles and squares in 0.5mm and whole-number-sized increments from 1mm to 10mm. The Positive Target features an opaque pattern on a clear background, whereas the Negative Target features a clear pattern on an opaque background.