

[See all 46 Products in Family](#)

Power Supply for 1.5-2.0mW HeNe Laser, 24 VDC, Bare Wire Leads



L28 Series with CDRH Delay HeNe Laser Power Supply

Stock **#11-385** [CONTACT US](#)

-

1

+

A\$560⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	A\$560.00 each
Need More?	Request Quote

Product Downloads



General

OEM

Type:

Compatible Laser Models:

1101, 1101P, 1103, 1103P, 1122, 1122P

L28 Series

Model Number:

Compatible Laser Stock Number:

#62-718, #62-719, #62-720, #62-721, #64-103, #64-104

Features:

CDRH Delay (3-5 seconds)

Physical & Mechanical Properties

4.00 x 1.50 x 1.00Dimensions (inches):

Electrical

8.33Output Power (W):

1.36 (Max. Current Draw)Input Current (A):

Hardware & Interface Connectivity

1700Output Voltage (V):

4.9Output Current (mA):

High Voltage Alden ConnectorConnector:

24 DCInput Voltage (V):

Regulatory Compliance

ViewCertificate of Conformance:

Product Details

- Power Options from 0.5 - 22.5mW
- Improved Stability
- Ideal for Interferometry and Metrology Applications
- Random or Linear Polarization Options

Lumentum High Performance Helium-Neon Lasers feature a patented close-cathode design that provides improved thermal and power stability. They also utilize a patented field concentrator design that enables fast turn-on. These Lumentum HeNe lasers also feature precisely aligned cylindrical housings, with cylindrical laser heads and electrical interconnect systems used to simplify system integration. Lumentum High Performance Helium-Neon Lasers' rugged design is ideal for even the most demanding applications. They are exemplary for use within interferometry and metrology applications.

Note: Please exercise caution when using a user-provided power supply to not exceed the electrical specifications of the laser as this may cause damage and void the warranty. These HeNe lasers comply with 21CFR1040 and IEC 825-1:1993. Lumentum was previously known as JDSU.

Technical Information

Beam Expander Mounting Configurations

Click on an item below to be brought to that item's product page.

