

[See all 78 Products in Family](#)

# Preloaded Norland Optical Adhesive NOA 72 Dispensing Barrel (10cc)

See More by [Norland](#)



10cc Dispensing Barrel for NOA (NOA60 shown as an example)

Stock **#17-365** **1 In Stock**

-

1

+

A\$63<sup>.20</sup>

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-4        | A\$63.20 each                 |
| Qty 5-11       | A\$56.96 each                 |
| Need More?     | <a href="#">Request Quote</a> |

Product Downloads

| General  |                 |
|----------|-----------------|
| 0.34     | Size (oz):      |
| 72       | Norland Number: |
| 4 months | Shelf Life:     |
| Barrel   | Type:           |

|                                                                                                                              |                                                 |
|------------------------------------------------------------------------------------------------------------------------------|-------------------------------------------------|
| <b>Typical Applications:</b><br>Bonding plastics or glass where low UV light transmission prevents curing of other adhesives |                                                 |
| <b>Note:</b><br>Contains 10g of adhesive                                                                                     |                                                 |
| <b>Optical Properties</b>                                                                                                    |                                                 |
| 1.56                                                                                                                         | <b>Index of Refraction (n<sub>d</sub>):</b>     |
| 315 - 450                                                                                                                    | <b>Absorption Range (nm):</b>                   |
| <b>Material Properties</b>                                                                                                   |                                                 |
| Excellent                                                                                                                    | <b>Glass Bonding:</b>                           |
| Good                                                                                                                         | <b>Metal Bonding:</b>                           |
| Excellent/Good                                                                                                               | <b>Plastic Bonding:</b>                         |
| 155                                                                                                                          | <b>Viscosity (cps):</b>                         |
| Plastic to Plastic/Glass                                                                                                     | <b>Bonding Type:</b>                            |
| 5                                                                                                                            | <b>Energy for Full Cure (J/cm<sup>2</sup>):</b> |
| <b>Environmental &amp; Durability Factors</b>                                                                                |                                                 |
| Hard & Resilient                                                                                                             | <b>Durability:</b>                              |
| <b>Regulatory Compliance</b>                                                                                                 |                                                 |
| <a href="#">Compliant</a>                                                                                                    | <b>RoHS 2015:</b>                               |
| <a href="#">View</a>                                                                                                         | <b>Certificate of Conformance:</b>              |
| <a href="#">Compliant</a>                                                                                                    | <b>Reach 251:</b>                               |

## Product Details

- Dispensing Syringes Preloaded with 2 or 10g of Adhesive
  - Adhesives for Glass, Metal, and Plastic Bonding
  - Require a Dispensing Unit & Dispenser Tips for Use
  - [Applicator and Bulk Bottles](#) of Norland Adhesive Also Available
- Preloaded Norland Optical Adhesive Syringes are pneumatic dispensing syringes preloaded with either 2g or 10g of Norland Optical Adhesive. Norland Optical Adhesives are one-part, UV curing adhesives that are used for glass, metal, and plastic bonding. A range of adhesives are available to meet specific application requirements such as MIL-A-3920 for defense applications, low outgassing for aerospace applications, or UV transmission for UV optical applications. Preloaded Norland Optical Adhesive Syringes require a [dispensing unit](#) and [dispensing tips](#) for use and are ideal for applications requiring precise control of the amount of applied adhesive. Applicators and Bulk Bottles of Norland Adhesive are also available.

## Technical Information

| NORLAND OPTICAL ADHESIVES (NOA) APPLICATION NOTES    |                                                                                                                                   |
|------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------|
| Title                                                | Description                                                                                                                       |
| <a href="#">Applying Adhesive</a>                    | Covers best practices to use when applying Norland Optical Adhesives to ensure an even adhesive layer while avoiding air bubbles. |
| <a href="#">Chemical Resistance of NOA</a>           | Covers the effects of various chemicals on Norland Optical Adhesives including acids, bases, and solvents.                        |
| <a href="#">Preventing Lens Separations with NOA</a> | Covers best practices to avoid adhesive failures when bonding optical elements.                                                   |
| <a href="#">Separating Lenses Bonded with NOA</a>    | Covers how to unbond optical elements bonded with Norland Optical Adhesives.                                                      |