

Olympus PLN 10X, Ph1, Phase Contrast Objective



Stock **#86-935** NEW **1 In Stock**

-

1

+

A\$1,008^{.00}

ADD TO CART

Volume Pricing	
Qty 1+	A\$1,008.00 each
Need More?	Request Quote

Product Downloads

General	
PLN10XPH	Model Number:
Microscope Objective	Type:
Phase Contrast	Style:
Olympus	Manufacturer:
Note: Requires Ph1 phase annulus for phase contrast observation	

Physical & Mechanical Properties	
2.2	Field of View (mm):
34.27	Length excluding Threads (mm):
24	Maximum Diameter (mm):
Optical Properties	
N/A	Compatible Cover Glass Thickness (mm):
18.00	Focal Length FL (mm):
10X	Magnification:
0.25	Numerical Aperture NA:
1.34	Resolving Power (μm):
4.40	Depth of Field (μm):
10.6	Working Distance (mm):
22	Field Number (mm):
45	Parfocal Length (mm):
N/A	Immersion Liquid:
440	Depth of Focus (μm):
Threading & Mounting	
RMS / 20.32mm x 36 TPI	Mounting Threads:
Regulatory Compliance	
View	Certificate of Conformance:

Product Details

- Flat-Field Plan Achromat Design for Sharp, Distortion-Free Images
- Precision Phase Ring Matching (Ph1, Ph2, Ph3) For Optimal Contrast
- Available In Multiple Magnifications (10X, 20X, 40X) Plus A 100X Oil Immersion Option
- Optimized For the UIS2 Optical System, Ensuring Seamless Integration with Olympus CX43

Olympus PLN Phase Contrast Objectives provide high-performance imaging for precise cellular analysis on the [Olympus CX43](#) microscope. These objectives are engineered for accurate phase contrast imaging across magnifications, offering excellent contrast and flat-field correction. Designed specifically for the UIS2 optical system, they deliver sharp, high-clarity images ideal for live, unstained specimens. Olympus PLN Phase Contrast Objectives, such as the 10X Ph1 ([#86-935](#)) and 100X Ph3 oil ([#87-013](#)), ensure reliable results across a wide range of biological applications. Their consistent quality and compatibility with standard Olympus phase contrast condensers make them a trusted choice for professional labs.