

[See all 4 Products in Family](#)

Olympus PLN 20X, Ph1, Phase Contrast Objective



Stock #86-936 NEW 1 In Stock

-

1

+

A\$1,208^{.00}

ADD TO CART

Volume Pricing	
Qty 1+	A\$1,208.00 each
Need More?	Request Quote

Product Downloads

General	
PLN20XPH	Model Number:
Microscope Objective	Type:
Phase Contrast	Style:
Olympus	Manufacturer:
Note: Requires Ph1 phase annulus for phase contrast observation	

Physical & Mechanical Properties	
1.1	Field of View (mm):
43.70	Length excluding Threads (mm):
24	Maximum Diameter (mm):
Optical Properties	
0.17	Compatible Cover Glass Thickness (mm):
9.00	Focal Length FL (mm):
20X	Magnification:
0.40	Numerical Aperture NA:
0.84	Resolving Power (μm):
1.72	Depth of Field (μm):
1.2	Working Distance (mm):
22	Field Number (mm):
45	Parfocal Length (mm):
N/A	Immersion Liquid:
688	Depth of Focus (μm):
Threading & Mounting	
RMS / 20.32mm x 36 TPI	Mounting Threads:
Regulatory Compliance	
View	Certificate of Conformance:

Product Details

- Flat-Field Plan Achromat Design for Sharp, Distortion-Free Images
- Precision Phase Ring Matching (Ph1, Ph2, Ph3) For Optimal Contrast
- Available In Multiple Magnifications (10X, 20X, 40X) Plus A 100X Oil Immersion Option
- Optimized For the UIS2 Optical System, Ensuring Seamless Integration with Olympus CX43

Olympus PLN Phase Contrast Objectives provide high-performance imaging for precise cellular analysis on the [Olympus CX43](#) microscope. These objectives are engineered for accurate phase contrast imaging across magnifications, offering excellent contrast and flat-field correction. Designed specifically for the UIS2 optical system, they deliver sharp, high-clarity images ideal for live, unstained specimens. Olympus PLN Phase Contrast Objectives, such as the 10X Ph1 ([#86-935](#)) and 100X Ph3 oil ([#87-013](#)), ensure reliable results across a wide range of biological applications. Their consistent quality and compatibility with standard Olympus phase contrast condensers make them a trusted choice for professional labs.