

Protective Window for #16-772

See More by [Jenoptik](#)



Protective Window

Stock **#17-684** 1 In Stock

-

1

+

A\$314^{.00}

ADD TO CART

Volume Pricing	
Qty 1+	A\$314.00 each
Need More?	Request Quote

Product Downloads

General

Jenoptik

Manufacturer:

[#16-772](#)

Compatible Lens:

Physical & Mechanical Properties

110.50

Diameter (mm):

View	Certificate of Conformance:
----------------------	-----------------------------

Product Details

- Ideal for High-Precision Material Processing and Laser Scanning Applications
- Large Scan Fields Up to 320mm x 320mm
- Wide Range of Focal Lengths from 108mm - 330mm
- [Jenoptik JENar™ Silverline™ F-Theta Scanning Lenses](#) Also Available

Jenoptik JENar™ F-Theta Scanning Lenses are designed to provide flat field at the image plane of scanning systems and are used in conjunction with [galvanometers](#), [beam expanders](#), and [laser sources](#). These F-Theta lenses feature a wide range of focal lengths and large scan fields. Optimized for common Nd:YAG, Yb:doped, and fiber laser sources, these lenses are available in wavelength ranges of 355nm, 515-540nm, and 1030-1080nm. With their patented stackable mounting technology, these lenses compensate for thermal stresses and improve the stability of the optical components, ensuring high-precision adjustment and position control in OEM systems. Jenoptik JENar™ F-Theta Scanning Lenses are ideal for high-precision laser material processing and laser scanning applications.

[Contact us](#) if your application requires Jenoptik JENar™ F-Theta Scanning Lenses or [Jenoptik JENar™ Silverline™ F-Theta Scanning Lenses](#) not shown on our website.