

[See all 5 Products in Family](#)

Coherent® High Sensitivity Optical Power Sensor 1098416 | IR, 800-1800nm

See More by [Coherent®](#)



Stock **#59-980** [CONTACT US](#)

-

1

+

A\$1,768^{.00}

ADD TO CART

Volume Pricing	
Qty 1+	A\$1,768.00 each
Need More?	Request Quote

Product Downloads

General	
OP-2 IR Coherent Part Number: 1098416	Model Number:
Meter required	Type:
±4.5	Calibration Uncertainty (%):
	Cooling Method:

Air	
Compatible Meters: #35-203, #12-393, #59-978, #88-411, #66-277, #88-412	
Physical & Mechanical Properties	
5.0	Active Area Diameter (mm):
Optical Properties	
800 - 1800	Wavelength Range (nm):
Sensor	
Germanium	Type of Sensor:
Electrical	
10	Maximum Incident Beam Power (mW):
10	Minimum Incident Beam Power (nW):
1	Resolution (nW):
10nW - 10mW	Power Range:
Hardware & Interface Connectivity	
1.8	Length of Cable (m):
DB-25	Computer Interface:
Regulatory Compliance	
Exempt	RoHS 2015:
Contains SVHC(s)	Reach 224:
View	Certificate of Conformance:

Product Details

- Utilize Silicon or Germanium Detectors
- Ideal for nW to Low mW CW Laser Measurements
- Removable Light Shield
- Compatible with [Coherent® Laser Power and Energy Meters](#)

Coherent® High Sensitivity Optical Power Sensors are semiconductor sensors designed for nanowatt to low milliwatt continuous wave laser measurements. These semiconductor sensors are available for detection from the ultraviolet to the infrared, and feature a removable light shield. An attenuator is also available that will boost power up to 5W.

Note: OP-2 sensors are compatible with the LabMax-Pro ([#35-203](#)), LabMax-TOP/TO ([#88-412](#)), FieldMaxII-TOP/TO ([#66-277](#)), and FieldMate ([#59-978](#)) meters.