

Schneider 80mm F-Mount Lens



Stock #34-235 3-5 DAYS

⊖ 1 ⊕ **A\$2,504.00**

ADD TO CART

Qty 1+
A\$2,504.00

Volume Pricing
[Request Quote](#)

Get Product Downloads

Field of View @ Min Working Distance (mm):
188 (35mm Sensor)

Iris Option:
Variable

Length (mm):
56.90

Filter Thread:
M43.0 x 0.75

Maximum Diameter (mm):
49.0

Weight (g):
280.00

Maximum Rear Protrusion (mm):
4.5

Maximum Image Circle (mm):
60.00

Horizontal Field of View, 35mm Sensor:
30.1°

Note:
Optimized Working Distance: 403 - 2062mm

Type:
Fixed Focal Length Lens

Focal Length FL (mm):
80.00

Maximum Sensor Format:
60mm (Image Circle)

Working Distance (mm):
403 - ∞

Mount:
F-Mount

Aperture (f/#):
f/4.0 - 4/16

Distortion (%):
<0.8

Coating:
400 - 1000 BBAR

Lens Wavelength Range:
VIS-NIR Color Corrected

Regulatory Compliance

RoHS 2015:
[Compliant](#)

Certificate of Conformance:
[View](#)

Reach 233:
[Compliant](#)