


[See all 29 Products in Family](#)

SCHOTT AS87ECO, 5mm Dia., 0.1mm Thick, Ultra-Thin Window

See More by [SCHOTT Optical Components](#)



Stock **#20-207** **20+ In Stock**

-

1

+

A\$49²⁰

ADD TO CART

Volume Pricing	
Qty 1-10	A\$49.20 each
Qty 11-49	A\$38.40 each
Need More?	Request Quote

Product Downloads

General

Type:

Protective Window

Physical & Mechanical Properties

Bevel:

Protective as needed

Clear Aperture (%):

90

Clear Aperture CA (mm):

4.50	
	Diameter (mm):
5.00 ±0.127	
	Thickness (mm):
0.10 ±0.01	
	Knoop Hardness (kg/mm²):
500.00	
	Poisson's Ratio:
0.22	
	Young's Modulus (GPa):
73.3	

Optical Properties	
	Abbe Number (v _d):
59.5	
	Coating:
Uncoated	
	Index of Refraction (n _d):
1.504	
	Substrate:
AS 87 ECO	
	Surface Quality:
80-50	
	Wavelength Range (nm):
200 - 3200	

Material Properties	
	Coefficient of Thermal Expansion CTE (10 ⁻⁶ /°C):
8.7	
	Density (g/cm³):
2.46	

Regulatory Compliance	
	RoHS 2015:
Compliant	
	Certificate of Conformance:
View	
	Reach 247:
Compliant	

Product Details

- High Level of Flexibility
- Ultra-Thin Thickness for Low Profile Designs
- Excellent Transmission from 250nm to >3µm

SCHOTT AS 87 ECO Ultra-Thin Windows feature an extremely thin and flexible design for applications requiring a rugged, low profile. These windows have excellent mechanical properties, including a high bending and impact strength, minimizing the possibility of damage under normal operating conditions. They also provide excellent transmission from the UV to the IR, enabling integration into applications that range from biomedical to IR imaging. SCHOTT AS 87 ECO Ultra-Thin Windows are manufactured through a draw-down process that virtually eliminates surface defects and provides the glass surfaces with an extremely low surface roughness. Common applications include their use as a cover glass for displays, fingerprint sensors, and touch panels, where their high scratch resistance prevents surface damage.

Quote Your Size