

PL-D775-AF-ED Pixelink USB 3.0 Autofocus Monochrome Camera (Recertified 05-P)



Stock #34-787-RCD-05P RECERTIFIED **1 In Stock**

[Similar Cameras](#)

A\$1,696⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	A\$1,696.00 each
Need More?	Request Quote

Product Downloads

General

PL-D775-AF-ED **Model Number:**

Monochrome Camera **Type:**

PL-D **Camera Series:**

Pixelink **Manufacturer:**

Physical & Mechanical Properties

Dimensions (mm):
55 x 38.5 x 27 (excludes connectors and lens mount)

Weight (g):
35.8

Housing:
Full

Sensor

Frame Rate (fps):
15.0000000000

Imaging Sensor:
ON Semi MT9P031

Pixel Size, H x V (µm):
2.2 x 2.2

Pixels (H x V):
2,592 x 1,944

Sensing Area, H x V (mm):
5.7 x 4.28

Pixel Depth:
8/12 bit

Shutter Type:
Rolling

Type of Sensor:
Progressive Scan CMOS

Exposure Time:
107µs - 2s

Sensor Format:
1/2.5"

Dynamic Range (dB):
60

Image Buffer:
Not Specified

Resolution (Megapixels):
5.0000000000

Machine Vision Standard:
USB3 Vision v1.0

Electrical

Power Consumption (W):
Not Specified

Hardware & Interface Connectivity

Connector:
USB 3.0, Micro-B with Screw Locks

Power Supply:
Power over USB

Synchronization:
Hardware Trigger (GPIO) or Software Trigger

Interface:
USB 3.0

Interface Port Orientation:
Back Panel

GPIOs:
1 opto-isolated trigger input, 1 opto-isolated output, 2 non-isolated outputs, 1 non-isolated input

GPIO Connector Type:
8-pin Hirose (HR25)

Threading & Mounting

Mount:
C-Mount

Mounting Threads:
1/4-20 with Tripod Mount Adapter [#34-949](#)

Environmental & Durability Factors

Operating Temperature (°C):
0 to +50

Storage Temperature (°C):
-45 to +85

Regulatory Compliance

Certificate of Conformance:
[View](#)

Product Details

- Seamless Integration of Liquid Lenses
- One-Push Autofocus, High Speed Focus Movement
- Easy to Use USB 3.0 Interface

Pixelink® USB 3.0 Autofocus Liquid Lens Cameras provide the ability to seamlessly integrate and control liquid lenses. By enabling the liquid lens to be directly connected to the camera, it allows for the camera to drive and control the liquid lens without the need of a separate driver to achieve fast, continuous focus control. This simple autofocus system makes these cameras ideal for high speed applications such as bar code reading, inspection, and biomedical applications. Pixelink® USB 3.0 Autofocus Liquid Lens Cameras are compatible with our [TECHSPEC® Liquid Lens Cx Series Fixed Focal Length Lenses](#), which combine high resolution image performance with built-in liquid lens integration.

To get started, choose a camera and find the appropriate Cx Lens Liquid Lens options listed under the Accessories section. These lenses are available in 12mm, 16mm, 25mm, 35mm, and 50mm focal lengths and are ready to mount to the Pixelink® USB 3.0 Autofocus Liquid Lens Cameras.

Note: Imaging lens with liquid lens sold separately. Choose one from Liquid Lens Cx Series Fixed Focal Length Lenses.

Pixelink Capture is a free, user-friendly application included with all Pixelink cameras, offering real-time image and video capture through an intuitive graphical interface. In contrast, the Pixelink SDK is a comprehensive development toolkit for Windows and Linux that enables developers to build custom applications with full camera control via C/C++, .NET, or Python. The SDK is available as a trial download, allowing users to evaluate its capabilities before purchasing a license. Links to software downloads (SDK and Capture) are available on the product pages.
