

## Single Mode Optical Fiber 450-600nm, 10m



Stock #72-896 **1 In Stock**

- 1 + A\$192.<sup>00</sup>

**ADD TO CART**

### Volume Pricing

Qty 1-4	A\$192.00 each
Qty 5-24	A\$172.80 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

### General

SM **Type:**

### Physical & Mechanical Properties

125.0 ± 1.0 **Cladding Diameter (µm):**

10 **Length (m):**

2.5 **Core Diameter (µm):**

245.0 ± 15.0

Coating Diameter:

## Optical Properties

0.13 Numerical Aperture NA:

≤ 12.0 dB/km @ 630 nm ≤ 30.0 dB/km @ 515 nm Attenuation (dB/km):

450 - 600 Wavelength Range (nm):

3.5 ± 0.5 @ 515 nm Mode Field Diameter (nm):

## Regulatory Compliance

[View](#) Certificate of Conformance:

## Product Details

- Single Mode and Polarization Maintaining Options
- 5, 10, and 20m Lengths
- Transmission Options from 450nm to 1625nm

Bare Fiber Strands are cladded step index fibers with no sheath manufactured by Coherent and Corning to allow for easy integration in space constrained systems. These fiber spools allow for direct access to the core, facilitating precise measurements and connections as well as allowing for modification to the lengths as needed. Featuring various wavelength ranges spanning the VIS and IR spectra, these fiber spools cover a wide range of applications that require specific wavelengths and provide tight cutoff tolerances. Bare Fiber Strands are designed with core diameters of 3.0µm up to 8.2µm and numerical apertures ranging from 0.12 to 0.14.