

## Thermopile Based Touchscreen Portable Laser Power Meter



Thermopile Based Touchscreen Portable Laser Power Meter, #34-515

Stock **#34-515** **3 In Stock**

⊖ 1 ⊕ A\$2,576<sup>00</sup>

**ADD TO CART**

### Volume Pricing

|            |                               |
|------------|-------------------------------|
| Qty 1-4    | A\$2,576.00 each              |
| Qty 5+     | A\$2,320.00 each              |
| Need More? | <a href="#">Request Quote</a> |

### Product Downloads

### General

17 **Operating Lifetime (hours):**

5 **Response Time (s):**

Touch screen color LCD **Type of Display:**

USB Port Available for Data Transfer **Note:**

## Physical & Mechanical Properties

181.40 **Length (mm):**

210 **Weight (g):**

41.00 **Width (mm):**

17.0 **Depth (mm):**

3 **Accuracy (%):**

## Optical Properties

190 - 20000 **Wavelength Range (nm):**

0.19 - 20 **Wavelength Range (μm):**

0.19 - 20μm **Spectral Range:**

0.248 - 2.5μm & 10.6μm **Calibrated Spectral Range:**

## Sensor

6 sec **Exposure Time:**

19mm Diameter **Maximum Sensor Size (mm):**

## Electrical

0.5W - 250W (average power) **Power Range:**

10 **Noise Equivalent Power (mW):**

## Hardware & Interface Connectivity

USB Rechargeable Battery **Power Supply:**

## Threading & Mounting

8-32 threaded (x2) **Mounting Hole for Screw:**

## Environmental & Durability Factors

65 **Maximum Temperature (°C):**

## Regulatory Compliance

[Compliant](#) **RoHS 2015:**

[View](#) **Certificate of Conformance:**

[Compliant](#) **Reach 242:**

## Product Details

- Small Portable Design with Touchscreen Display
- Computer and Software Not Required
- High Damage Threshold
- USB Rechargeable Battery

Touchscreen Portable Laser Power Meters feature LCD displays with touchscreen controls, the ability to adjust wavelength, brightness and screen orientation, and min/max display. Available in two designs, one as a silicon based sensor and the other an absorber, these portable power meters can transfer data to a computer for data logging via a mini USB port. The silicon sensor model (#34-514) features a folding body design with a click stop at 90 degrees, providing the unique ability of being placed on an optical table unmounted when oriented at 90 degrees. If the beam height is 78mm off the optical table, you can simply set the folded power meter directly onto the table. Both Touchscreen Portable Laser Power Meter models feature 8-32 mounting holes for table top mounting and rechargeable battery.

**Note:** Mini-USB cable not included.