

[See all 36 Products in Family](#)

## Triple Bandpass Green-Red-NIR Filter M37



Stock #74-604 NEW 1 In Stock

- 1 + A\$761.<sup>00</sup>

**ADD TO CART**

### Volume Pricing

Qty 1+	A\$761.60 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

**Full Width-Half Max FWHM Range (nm):**  
20nm, 20nm, 45nm ±10 nm

### General

**Type:**  
Triple Bandpass Mounted Imaging Filter

**Model Number:**  
TB550/660/850-37

### Physical & Mechanical Properties

**Outer Diameter (mm):**  
39

**Substrate Thickness (mm):**

2mm

## Optical Properties

Green-Red-NIR **Color:**

40/20 **Surface Quality:**

≥85% **Transmission (%):**

543-558nm, 653-668nm, 835-865nm **Transmission Wavelength (nm):**

## Threading & Mounting

M37 x 0.75 **Filter Thread:**

5.2 **Mount Thickness (mm):**

## Regulatory Compliance

[View](#) **Certificate of Conformance:**

## Product Details

- Block and Transmit Desired Key MS and NIR Spectral Bands with One Filter
- Remove The Need for Dual Sensor Setups
- Anti-Reflection Coating for Durability and Performance
- Various Mounting Thread Options Available

Multi-Band Machine Vision Bandpass Filters feature both double or triple bandpass options in one filter, allowing for greater flexibility in system design. These filters are designed with up to ≥90% transmission in the visible (MS) or near-infrared (NIR) spectra with various wavelength range combinations available. Additionally, these filters are AR coated for optimal transmission and feature a hard-coated, single-substrate design with superior surface quality to maximize optical performance. Multi-Band Machine Vision Bandpass Filters ensure accurate color reproduction by blocking unwanted wavelengths, eliminating the need for dual-sensor imaging. These filters are ideal for surveillance applications such as, security and intelligent traffic management, as well as normalized difference vegetation index (NDVI) imaging applications.

**Note:** Other filter threads are available upon request.