

Reflectance Integrating Sphere

See More by [Ocean Optics](#)



Stock #90-587 **NEW** 1 In Stock

⊖ 1 ⊕ A\$5,734⁴⁰

ADD TO CART

Volume Pricing

Qty 1+	A\$5,734.40 each
Need More?	Request Quote

Product Downloads

Diameter of Entrance Port (mm):
10.32

Fiber Connector Type:
SMA905

General

Model Number:
ISP-REFL

Note:
Provides even surface illumination for reflectance

measurements of surfaces such as the color of flat samples

900 hours **Lamp Lifetime (hours):**

Reflectance Integrating Sphere **Title:**

Physical & Mechanical Properties

864.7 **Weight (g):**

54 x 57 x 83 **Dimensions (mm):**

38.10 **Diameter (mm):**

Optical Properties

Spectralon® doped with BaSO₄ **Coating:**

~360–2500 nm **Spectral Range:**

Environmental & Durability Factors

3100 **Color Temperature (K):**

Regulatory Compliance

[Compliant](#) **RoHS 2015:**

[View](#) **Certificate of Conformance:**

[Compliant](#) **Reach 250:**

Product Details

- Measure Total Irradiance or Reflectance with Models Optimized for Emission Sources or Surface Illumination
- Ideal for UV–NIR Applications in Materials Testing, LEDs, Lasers, and More
- White Reflectance Standard Provides Stable, Repeatable Reference Measurements
- Compatible with Ocean Optics Spectrometers and Accessories

Ocean Optics integrating spheres provide flexible, accurate solutions for measuring light output or surface reflectance across a wide spectral range. Whether you need 360° field-of-view irradiance collection, uniform surface illumination for reflectance measurements, or a stable reference for calibration, these integrating spheres ensure consistent, reliable results. The White reflectance standard ([#90-586](#)) complements the spheres by providing a dependable calibration reference for diffuse reflectance measurements. Ocean Optics Integrating Spheres are well-suited for UV-NIR applications, including material testing, LED analysis, and laser measurements.

Selection Guide:

FOIS-1 ([#90-588](#)): Best for **irradiance measurements** and light emission sources; features a 360° field of view for collecting light from LEDs, lasers, and other broad light fields.

ISP-REF ([#90-587](#)): Best for **surface reflectance measurements**; provides even surface illumination and integrates a transfer optic and built-in light source for easy measurement of color or reflectivity on opaque or directional samples.

WS-1 ([#90-586](#)): Use alongside your integrating sphere for reliable white reference measurements when calibrating for diffuse reflectance.