

UV Curing Oven



Stock **#26-822** 2 In Stock

-

1

+

A\$8,165⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	A\$8,165.00 each
Need More?	Request Quote

Product Downloads

Physical & Mechanical Properties	
14	Weight (kg):
190 x 175 x 185	Chamber Size D x W x H (mm):
246 x 282 x 410	Dimensions (mm):
Optical Properties	

365.00	Wavelength (nm):
0.25 Max	Irradiance (W/cm²):
Hardware & Interface Connectivity	
AC 100 - 305V	Power Requirement:
Regulatory Compliance	
View	Certificate of Conformance:

Product Details

- Up to 250mW/cm² UV Irradiance
 - 365nm Center Wavelength
 - Digital Control of UV Intensity and Exposure Time
- The UV Curing Oven is a compact 246 x 282 x 410mm UV LED curing chamber that can provide high intensity UV irradiance up to 250mW/cm2 for fast curing. Featuring a digital controller, UV light intensity can be fixed between 10% and 99% with adjustable exposure times ranging from 1 second to 100 minutes. UV reflective panels in the curing chamber provide homogeneity greater than 85% on the irradiated surface for reliable and repeatable UV emission. The UV Curing Oven is ideal for a wide range of bonding, curing, drying, hardening, and photolithography applications. A UV protection system between the lamp and the door avoids unwanted UV exposure by shutting off the UV illumination if the door is open.

FAQ(s)

- Is the UV curing oven safe to operate?**
Yes. It features a door interlock system, 99.9% UV-blocking viewing window, and auto shut-off to prevent accidental UV exposure.
- What are common applications of UV curing ovens?**
Typical uses include bonding, drying, hardening, photolithography, and curing specialty inks, adhesives, and coatings in research and industrial settings.