

UV Radiometer Unit



UV Radiometer Unit, #88-136

Stock **#88-136** 1 In Stock

-

1

+

A\$1,856⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	A\$1,856.00 each
Need More?	Request Quote

Note: This item requires accessories for use | [Learn More](#)

Product Downloads

General

3.5 digit LCD	Type of Display:
2.8 readings/sec	Conversion Rate:

Physical & Mechanical Properties

0.3	Weight (kg):
-----	--------------

157 x 51 x 91	Dimensions (mm):
± 2	Accuracy (%):
Electrical	
Switchable: 0 – 20 mW/cm ₂ 0 – 200 μW/cm ₂ 0 – 2000 μW/cm ₂	Intensity Range:
Hardware & Interface Connectivity	
9 V Battery (not included)	Power Requirement:
Regulatory Compliance	
View	Certificate of Conformance:

Product Details

- Designed to Detect UV Wavelengths from 250 – 380nm
- NIST Certified Sensors
- 9V Battery Provides up to 120 Hours of Operation
- Requires One NIST Traceable Sensor for Operation

The NIST Certified UV Radiometer is ideal for inspecting ultraviolet light sources in a variety of quality control applications. The NIST Certified UV Radiometer is powered by a standard 9V battery for up to 120 hours of operation. Three NIST certified interchangeable sensors are available to detect a wide range of ultraviolet wavelengths from 250 – 380nm. The NIST Certified UV Radiometer’s range switch allows the selection of three intensity ranges.

Note: The UV Radiometer Unit ([#88-136](#)) requires one NIST Traceable Sensor ([#88-137](#), [#88-138](#), or [#88-139](#)) for operation.