

# UV-VIS Heavy-Duty Transmission Dip Probe

See More by [Ocean Optics](#)



Stock #90-569 NEW **1 In Stock**

⊖ 1 ⊕ A\$3,704<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1+	A\$3,704.00 each
Need More?	<a href="#">Request Quote</a>

Product Downloads

**Fiber Connector Type:**  
SMA905

**General**

**Model Number:**  
TI300-UV-VIS

**Note:**  
Breakout 1 meter from end of the probe

**Optical Properties**

**Wavelength Range (nm):**  
200 - 1100

## Regulatory Compliance

[Compliant](#)

RoHS 2015:

[View](#)

Certificate of Conformance:

[Compliant](#)

Reach 250:

## Product Details

- Transmission Dip Probes Designed for Reliable In-Solution Absorbance/Transmission Measurements
- Rugged Stainless Steel or PEEK for Tough Process Conditions and Harsh Environments
- Flexible Path Lengths Available with Interchangeable Probe Tips
- Compatible with Ocean Optics Spectrometers and Accessories

Ocean Optics Transmission Dip Probes couple to spectrometers and light sources to measure absorbance and transmission in solutions. Choose from ruggedized high-pressure probe ([#90-569](#)) for demanding process environments or PEEK-jacketed probes ([#90-570](#) and [#90-571](#)) for harsh chemical conditions, spanning UV-VIS to VIS-NIR wavelengths. Easily customize your setup with accessories such as interchangeable probe tips in various path lengths and the protective sleeve ([#90-585](#)) for extended durability in corrosive or high-temperature applications. Ocean Optics Transmission Dip Probes are designed for seamless integration with [Ocean Optics spectroscopy systems and compatible accessories](#).