

TECHSPEC® Visible Plate Beamsplitter Kit, 25mm Diameter



Stock #83-388 [CONTACT US](#)

-

1

+

A\$864^{.00}

ADD TO CART

Volume Pricing	
Qty 1+	A\$864.00 each
Need More?	Request Quote

Product Downloads

General

Note:
Beamsplitter-coated side is marked with a black dot

Number of Filters:
5: [#47-240](#), [#68-385](#), [#45-852](#), [#68-403](#), [#48-398](#)

Type:
Standard Beamsplitter

Physical & Mechanical Properties

Construction:
Plate

Optical Properties	
Coating Specification: Surface 1: R/T ±5% @ 550nm, R _{avg} ±10% 400 - 700nm Surface 2: AR R _{avg} ≤1%, R _{abs} ≤2% 400 - 700nm	
Wavelength Range (nm): 400 - 700	

Regulatory Compliance	
Certificate of Conformance: View	

Product Details

- Many Beamsplitting Ratios Available
- Visible and NIR Coating Options Offered
- Multi-Layer AR Coated Second Surface
- **C-Mounted Plate Beamsplitters** Also Available

TECHSPEC® Visible and NIR Plate Beamsplitters are ideal for dual magnification **imaging** systems and for combining low power **laser** beams. These beamsplitters offer the optimum combination of polished, high-quality optical-grade glass with minimum substrate thickness. The broadband dielectric coatings provide maximum throughput, are ideal for minimizing ghost images, and have much less energy loss than metallic coatings. TECHSPEC® Visible and NIR Plate Beamsplitters are coated on their back surfaces with a multi-layer anti-reflection (AR) coating, reducing back reflections to less than 1.0% for each wavelength range. Note that for easy identification, the coated side of the beamsplitter is marked with a black dot.

Technical Information

